


PICO841

Pico-ITX SBC with Intel Atom® Processor E3845, LVDS/VGA, LAN and Audio

Features

- Intel Atom® processor E3845/E3827
- 1 DDR3L-1066/1333 SO-DIMM, up to 8GB
- 4 USB 2.0 ports
- 2 COM ports
- 2 PCI Express Mini Card slots



Core System



CPU	Intel Atom® processor E3845 quad core onboard (Bay Trail)
System Memory	1 x 204-pin DDR3L-1066/1333 SO-DIMM, up to 8GB
Chipset	SoC integrated
BIOS	AMI
SSD	N/A
Watchdog Timer	255 levels, 1 to 255 sec.
Expansion Interface	1 x full-size PCI Express Mini Card slot with mSATA 1 x half-size PCI Express Mini Card slot
Battery Lithium	Lithium 3V/220mAH
Power Input	1 x 4-pin connector +12V DC-in only AT Auto Power On function supported
Power Requirements	Intel Atom® E3845 @ 1.91 GHz, 8GB DDR3L Max. RMS: +12V @ 1.49A
Size	100 x 72 mm
Board Thickness	1.6 mm
Temperature	-20°C to +70°C (-4°F to +158°F), operation
Relative Humidity	10% - 95% relative humidity, non-condensing

I/O


MIO	2 x RS-232/422/485
SATA	1 x SATA-300
Hardware Monitoring	Detect CPU/system temperature and voltage
Ethernet	1 port 10/100/1000 Mbps supports Wake-on-LAN, PXE Boot ROM with Intel® i211AT
Audio	HD Codec audio as MIC-in/Line-out with Realtek ALC888S
USB	4 x USB 2.0
SMBus	System Management Bus for advanced monitoring/control
Digital I/O	NA
TPM	ST ST33TPM12LPC with TPM 1.2 compliant

Display

Chipset	Intel® HD Graphics
Memory Size	Share system memory
Display Interface	1 x VGA 1 x LVDS; 18/24-bit single/dual channel



▲ Rear view



▲ Assembly view

Packing List

Standard

Quick installation guide, User's Manual/Utility CD and cable

Accessories

Part Number	Description	Qty
85932831000E	AX93283 I/O board	1
85932671000E	AX93267 I/O board	1
59406308010E	SATA cable	1
594H3130600E	SATA power cable	1
5078H843000E	Heatspreader	1
5078H100200E	Heatsink	1

Optional

Part Number	Description
594H8302800E	USB cable 20 x 2P, P=2.0 mm, L=200 mm
594H8303000E	Audio cable 20 x 2P, P=2.0 mm, L=200 mm
594H8301600E	Power/Reset button + LED cable
594H8302100E	COM cable 10 x 2P, P=2.0 mm, L=200 mm
59340000200E	USB + audio + LED cable, L=200 mm

Ordering Information

Standard

PICO841VGA-E3845 (P/N: E38H841104)	Pico-ITX SBC with Intel Atom® processor E3845 (1.91 GHz, 2 MB Cache, 10 W), VGA/LVDS, 1 GbE LAN, audio and gift box
---------------------------------------	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Axiomtek:](#)

[PICO841VGA-E3845 w/IO & ACCESSORIES](#)