





Verpackt im Gurt in Anlehnung an DIN IEC 60286-3
tape on reel packaging according to DIN IEC 60286-3
 Verpackungseinheit: 160 Stück
packaging unit: 160 pcs




Anforderungsstufe 1
performance level 1

Kontaktbereich vergoldet
mating area gold plating

Anschlussbereich verzinnt 4-6 μm
terminal area 4-6 μm tin plating

Koplanarität der Anschlüsse $\leq 0,1 \text{ mm}$
coplanarity area of termination $\leq 0,1 \text{ mm}$



Leiterplatten-Layout Vorschlag für SMT



BA 7-23 - hohe Bauhöhe

type 7-23 - high profile

Dimension no.		Tolerances				Scale 2:1					
		ISO 8015		All Dimensions in mm		Material					
<u>Customer drawing:</u> All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.		Subject to modification without prior notice. Drawing will not be updated.		Federl. SMC-B 50-SMD-BA7-23 Female SMC-B 50-SMD-type7-23							
<table><tr><td>g</td><td>30.01.2020</td></tr><tr><td>Index</td><td>Date</td></tr></table>		g	30.01.2020	Index	Date			ERNI International AG Zürichstrasse 72 8306 Brüttisellen - Zürich Switzerland		234199	
g	30.01.2020										
Index	Date										
				Class		SMCB					
						I A3					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[234199](#)