






Stecklänge / mating length




E = early mate, late break / voreilend

S = standard

L = late mate, early break / nacheilend



Bestückungsplan / contact layout



Steckseite ACE / Anschlussseite GA 3,8mm /
contact side ACE / terminal Side straight 3,8mm
Lötanschluss 0,6 x 0,6 / solder terminal 0,6 x 0,6
Isolierwerkstoff / housing material : PBT GF 30


Bauart 4 / Type 4

Anforderungsstufe 2 = 400 Steckzyklen / performance class 2 = 400 mating cycles

Fehlende Maße und Angaben gemäss IEC 60603-2 / DIN EN 60603-2

Missing information and dimensions according to IEC 60603-2

Leiterplatten-Lochbild / PCB drillhole pattern



Copyright by ERNI GmbH
Proper early notice pursuant to ISO 16016 is to be observed.

Information:				Tolerances		 All Dimensions in mm		Scale		2:1	
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.				Subject to modification without prior notice. Drawing will not be updated.				Designation Messerleiste E48 Löt <i>Male Con. E48 Solder</i>			
				a		13.09.2010				www.ERNI.com	
Index		Date						Class		STVE	
										A3	

Copyright by ERNI GmbH
Proprietary notice pursuant to ISO 16016 to be observed.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[364891](#)