






Bestückungsplan / *contact layout*


Leiterplatten- Lochbild / *PCB drillhole pattern*



Tauchlötanschluss 0,3 x 0,7mm
solder terminal 0,3 x 0,7 mm

Anforderungsstufe 2 = 400 Steckzyklen
performance class 2 = 400 mating cycles

Fehlende Maße und Angaben nach IEC 60 603-2 / DIN EN 60 603-2
Missing information and dimensions per IEC 60 603-2 / DIN EN 60 603-2

Dimension no.			Tolerances Dim. for Information ISO 8015		 All Dimensions in mm		Scale 2:1	
<u>Customer drawing:</u> All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.			Subject to modification without prior notice. Drawing will not be updated.		DIN 41612 / IEC-60603-2 Female Connector R/2 48 Solder Type 7			
b			27.04.2021				ERNI International AG Zürichstrasse 72 8306 Brüttisellen - Zürich Switzerland	
Index			Date		Class STVR/2		I A3	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[284325](#)