






Stecklänge / mating length




E = early mate, late break / voreilend
S = standard



Stecklänge
mating length

Bestückungsplan / contact layout



Flachstecker 6,3 x 0,8 mm / Slip-on tabs 6,3 x 0,8 mm

Isolierwerkstoff / housing material : PC GF30

Bauart 3 / type 3

Anforderungsstufe 1 = 500 Steckzyklen / performance class 1 = 500 mating cycles

Fehlende Maße und Angaben gemäß IEC 60 603-2 / DIN EN 60 603-2

Missing information and dimensions according to IEC 60 603-2

Information:	Tolerances	 All Dimensions in mm	Scale	2:1
			Designation	
All rights reserved. Only for information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.	Subject to modification without prior notice. Drawing will not be updated.	 www.ERNI.com	Messerleiste H 11 Male Connector H 11	
			233226	I
a	27.11.2006			
Index	Date	V:00059913.SZA	STVH11	

Consider protection memo from DIN 34

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[233226](#)