






Stecklänge / mating length




E = early mate, late break / voreilend

S = standard


L = late mate, early break / nacheilend



Bestückungsplan / contact layout



Leiterplatten-Lochbild / PCB drillhole pattern



Steckseite AC / Anschlussseite AC / contact side AC / terminal Side AC

Lötanschluss 0,6 x 0,6 / solder terminal 0,6 x 0,6

Isolierwerkstoff / housing material : PBT GF 30

Bauart 4 / Type 4

Anforderungsstufe 1 = 500 Steckzyklen / performance class 1 = 500 mating cycles

Fehlende Maße und Angaben gemäss IEC 60603-2 / DIN EN 60603-2

Missing information and dimensions according to IEC 60603-2

Bedruckung siehe Zeichnung 294905

Marking see drawing 294905

Information:				Tolerances				Scale		2:1	
						All Dimensions in mm					
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.				Subject to modification without prior notice. Drawing will not be updated.		Designation Messerleiste D32 Löt <i>Male con. D32 solder</i>					
								www.ERNI.com		354867	
-		21.10.2008									
Index		Date				Class		STVD			

Copyright by ERNI GmbH
Proprietary notice pursuant to ISO 1016 to be observed.

Copyright by ERNI GmbH
Proprietary notice pursuant to ISO 16016 to be observed.

ERNI www.ERNI.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[354867](#)