








Verpackt im Gurt in Anlehnung an DIN IEC 60286-3
Tape on Reel Packaging according to DIN IEC 60286-3
Verpackungseinheit: 400 Stück
Packaging unit: 400 pcs



Leiterplatten-Layout Vorschlag / PCB-layout proposal



1) Durchmesser des Bohrers / Drill tool

Für weitere Layout Details bitte
MicroSpeed Applikations Schrift beachten.
For further layout details please consider
MicroSpeed application note.

Anforderungsstufe 1
Performance Level 1

Kontaktbereich vergoldet
Mating Area gold plating

Anschlussbereich verzinkt 4-6 µm
Terminal Area 4-6 µm tin plating

Koplanarität der Anschlüsse ≤ 0,1 mm
Coplanarity Area of Termination ≤ 0,1 mm

BlindMate SMD

Copyright by ERNI Production GmbH, L. Co. AG
From delivery notice pursuant to ISO 1008 to be observed

Information:		Tolerances			Scale	5:1
				All Dimensions in mm		
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.		Subject to modification without prior notice. Drawing will not be updated.			Designation	
					MSpeed Messerl. 90° PM <i>MSpeed male 90° PM</i>	
d		26.05.2015		ERNI		www.ERNI.com
Index		Date		364703		
					Class	MSPPM
						I A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[364703](#)