









Leiterplatten-Layout Vorschlag / *PCB-layout proposal*




1) Durchmesser des Bohrers / *drill tool*

Verpackt in Gurtverpackung
Tape on Reel Packaging
 Verpackungseinheit: 220 Stück
Packaging unit: 220 pcs



Abspulrichtung - *Reel off Direction* →




Anforderungsstufe 1
Performance Level 1

Kontaktbereich vergoldet
Mating Area gold plating

Anschlussbereich verzinnt 4-6µm
Terminal Area 4-6µm tin plating

Koplanarität der Anschlüsse ≤ 0,1mm
Coplanarity Area of Termination ≤ 0,1mm

Information:			Tolerances	 All Dimensions in mm	Scale	5:1
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.			Subject to modification without prior notice. Drawing will not be updated.		Designation	
					M10 MSpeed Blind Mate PM SMD	
e	10.09.2012		 www.ERNI.com		354281	
Index	Date				I A3	
					Class	MSPEED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[354281](#)