




Stecklänge / mating length



E = early mate, late break / voreilend

S = standard

L = late mate, early break / nacheilend



Gerader Anschluss 0,6x0,6mm / straight terminal 0,6x0,6mm

Isolierwerkstoff / housing material : PBT GF 30


Bauart 4 / type 4

Anforderungsstufe 2 = 400 Steckzyklen / performance class 2 = 400 mating cycles


Fehlende Maße und Angaben nach IEC 60 603-2 / DIN EN 60 603-2

Missing information and dimensions per IEC 60 603-2 / DIN EN 60 603-2

Bestückungsplan / contact layout



Leiterplatten-Lochbild / PCB drillhole pattern



Copyright by ERNI GmbH
Proprietary notice pursuant to ISO 16016 to be observed.

Proprietary notice pursuant to ISO 16101 to be observed.

Information:				Tolerances		 All Dimensions in mm		Scale		2:1			
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.				Subject to modification without prior notice. Drawing will not be updated.				Designation					
								Messerleiste Q, 64 Löt <i>Male Connector Q, 64 Solder</i>					
												www.ERNI.com	
		12.01.2011						364843				I	
Index		Date						Class				STVQ	
												A3	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[364843](#)