









ohne Ansaughaube / without hood




ohne Ansaughaube / without hood



Ansaughaube / hood




Kontaktbezeichnung
contact marking




Layoutvorschlag
recommended layout


Kontaktbezeichnung bei Pin 1
contact marking at pin 1



Verpackt im Gurt in Anlehnung an DIN IEC 60286-3
tape on reel packaging according to DIN IEC 60286-3
Verpackungseinheit: 440 Stück
packaging unit: 440 pcs



Abspulrichtung - Reel off direction




Anforderungsstufe 1
performance level 1

Kontaktbereich vergoldet
mating area gold plating

Anschlussbereich verzinkt 4-6 µm
terminal area 4-6 µm tin plating

Koplanarität der Anschlüsse ≤ 0.1 mm
coplanarity area of termination ≤ 0.1 mm

504408		rot red	1.5	
504407		grün green	1.5	
504406		blau blue	0.5	
504405		schwarz black	0.5	
Ident-Nr. part-no.	Codierung coding	Farbe colour	A	Bemerkung remark

Information:				Tolerances ISO 2768-FH ISO 8015		 All Dimensions in mm		Scale 5:1			
				Subject to modification without prior notice. Drawing will not be updated.		Designation M 1.27 MCB-P SMT 05-pin					
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.								www.ERNI.com		504404	
				A2							
b		31.07.2018						Class		MCBP	
Index		Date									

Copyright by ERNI Production GmbH & Co. KG
Proprietary notice pursuant to ISO 16046 to be observed.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[504405](#)