











Verpackt im Gurt in Anlehnung an DIN IEC 60286-3
tape on reel packaging according to DIN IEC 60286-3
Verpackungseinheit: 900 Stück
packaging unit: 900 pcs



Sperrfläche für Leiterbahnen gültig bei Verwendung von
Gegenstecker Federleiste 90° in IDC Ausführung
Restricted area for conductors valid for use by mating
female connector 90° in IDC version

Layoutvorschlag recommended layout



Kontaktbezeichnung bei Pin 1
contact marking at pin 1

Anforderungsstufe 1
performance level 1

Kontaktbereich vergoldet
mating area gold plating

Anschlussbereich verzinkt 4-6 µm
terminal area 4-6 µm tin plating

Koplanarität der Anschlüsse ≤ 0,1 mm
coplanarity area of termination ≤ 0,1 mm

514892		rot red	2.25	
514891		grün green	2.25	
514890		blau blue	0.75	
514889		schwarz black	0.75	
Ident-Nr. part-no.	Codierung coding	Farbe colour	A	Bemerkung remark

Copyright by ERNI Production GmbH & Co. KG
Proprietary notice pursuant to ISO 9001:4 to be observed.

Information:				Tolerances ISO 2768-FH ISO 8015		 All Dimensions in mm		Scale 5:1	
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.				Subject to modification without prior notice. Drawing will not be updated.		Designation M 1.27 MCB-A SMT 09-pin			
								514888	
b		31.07.2018				Class MCBA			
Index		Date							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[514889](#)