

## Special Contacts For Type L, M And N



### Ordering Information For Coax Contacts

| Characteristic Impedance | Contact Version                       | Cable Type                       | Part Number   |
|--------------------------|---------------------------------------|----------------------------------|---------------|
| 50 Ohm                   | Male; Crimp-Version                   | RG 178 B/U; RG 196 A/U           | <b>013686</b> |
| 50 Ohm                   | Female; Crimp-Version                 | RG 178 B/U; RG 196 A/U           | <b>013687</b> |
| 50 Ohm                   | Male; PCB-Solder-Version; Right Angle |                                  | <b>053299</b> |
| 50 Ohm                   | Female; Crimp-Version                 | RG 316 Protected                 | <b>053395</b> |
| 50 Ohm                   | Male; Crimp-Version                   | RG 316 Protected                 | <b>053400</b> |
| 50 Ohm                   | Female; Crimp-Version                 | RG 174 /U; RG 188 A/U; RG 316 /U | <b>054238</b> |
| 50 Ohm                   | Male; Press-Fit-Version; Right Angle  |                                  | <b>104875</b> |
| 50 Ohm                   | Female; Crimp-Version                 | RG 174 /U; RG 188 A/U; RG 316 /U | <b>594207</b> |
| 50 Ohm                   | Male; Crimp-Version                   | RG 174 /U; RG 188 A/U; RG 316 /U | <b>594213</b> |
| 50 Ohm                   | Female; Press-Fit-Version R1          |                                  | <b>914382</b> |
| 75 Ohm                   | Male; PCB-Solder-Version; Right Angle |                                  | <b>053306</b> |
| 75 Ohm                   | Male; Crimp-Version                   | RG 179 B/U; RG 187 A/U           | <b>053408</b> |
| 75 Ohm                   | Female; Crimp-Version                 | RG 179 B/U; RG 187 A/U           | <b>053410</b> |

### Ordering Information for High Power Contacts

| Max. Current | Contact Version                     | Comments                                                | Part Number   |
|--------------|-------------------------------------|---------------------------------------------------------|---------------|
| 10 A         | Female; Crimp-Version               |                                                         | <b>594178</b> |
| 20 A         | Female; Crimp-Version               |                                                         | <b>594180</b> |
| 30 A         | Female; Crimp-Version               |                                                         | <b>053452</b> |
| 40 A         | Female; Crimp-Version               |                                                         | <b>594182</b> |
| 40 A         | Female; Press-Fit-Version R3        |                                                         | <b>044965</b> |
| 10 A         | Female; Solder-Version              |                                                         | <b>594172</b> |
| 20 A         | Female; Solder-Version              |                                                         | <b>594174</b> |
| 40 A         | Female; Solder-Version              |                                                         | <b>594176</b> |
| 40 A         | Female; Solder-Version; Right Angle |                                                         | <b>053298</b> |
| 10 A         | Male; Crimp-Version                 |                                                         | <b>594227</b> |
| 20 A         | Male; Crimp-Version                 | First Made Last Break; Only Usable With Part No. 044965 | <b>053430</b> |
| 20 A         | Male; Crimp-Version                 |                                                         | <b>594229</b> |
| 30 A         | Male; Crimp-Version                 |                                                         | <b>033319</b> |
| 40 A         | Male; Crimp-Version                 |                                                         | <b>594231</b> |
| 10 A         | Male; Press-Fit-Version R1          | First Made Last Break                                   | <b>103855</b> |
| 40 A         | Male; Press-Fit-Version R1          | First Made Last Break; Only Usable With Part No. 044965 | <b>044846</b> |
| 40 A         | Male; Press-Fit-Version R1          |                                                         | <b>044847</b> |
| 10 A         | Male; Solder- Version               |                                                         | <b>594221</b> |
| 20 A         | Male; Solder- Version               |                                                         | <b>594223</b> |
| 40 A         | Male; Solder- Version               |                                                         | <b>594225</b> |
| 10 A         | Male; Solder-Version                | First Made Last Break; Only Usable With Part No. 044965 | <b>053444</b> |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[044965](#) [044846](#)