

Actuator

14-
060.207

Distribution by
Mouser



<https://mouser.eao.com/p/14-060.207>

Your product:



14-060.207 Actuator

FRONT

Front form: round

MOUNTING

Design: raised

Mounting cut-out: Ø 22.3 mm

Mounting type: Panel mounting

OPERATING-/INDICATION PART

Lens cap material: Plastic

Lens cap optical effect: transparent

Illumination colour: Red

ELECTRICAL CHARACTERISTICS

Operating voltage: 24 V AC/DC

Operation current: - 50

Electrical lifetime: 50 000 h

MECHANICAL CHARACTERISTIC

Terminal: Push-in terminal

Tightening torque: Fixing nut min. 0.8 Nm

Wire cross section:
wire 0.2 ... 1.0 mm²
wire 0.2 ... 0.75 mm² with core and sleeve
wire 0.2 ... 1.0 mm² without core and sleeve

Weight: 0.012 kg

AMBIENT CONDITION

IP Protection: IP20 rear side, IP65, IP67, IP69K front side, according to EN IEC 60529

Operating temperature: – 25 °C ... + 60 °C

Storage temperature: – 40 °C ... + 85 °C

Shock resistance: Max. 300 m / s², pulse width 18 ms (sinusoidal EN IEC 60068-2-27)

Vibration resistance: Max. 100 m / s² from 10 Hz ... 500 Hz, (sinusoidal EN IEC 60068-2-6)

Climate resistance: Damp heat, steady: 56 days, + 40 °C/93 % relative humidity, according to EN IEC 60068-2-78
Rapid change of temperature: 5 cycles, – 40 °C ... + 85 °C, as per EN IEC 60068-2-14

CERTIFICATE

Approbations: UL

Conformities: CE, UKCA

REACH: REACH compliant

RoHS: RoHS compliant

OTHER


Short Description: Actuator, Ø 22.3 mm, round, Push-in terminal, Red

Kind of illumination: Single-LED


Housing colour: Black

Housing material: Plastic


Wiring diagrams:



Mounting cut-outs:



Dimension drawings:



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[14-060.207](#)