

Actuator

31-
810.005



<https://eao.com/p/31-810.005>

Your product:



31-810.005 Actuator

FRONT

Front dimension:	24 mm x 18 mm
Front form:	rectangular
Front bezel colour:	Black
Front bezel material:	Plastic

MOUNTING

Design:	raised
Mounting cut-out:	Ø 16 mm
Mounting type:	Panel mounting

ELECTRICAL CHARACTERISTICS

Operating voltage:	10 - 55 V AC
Switching voltage and switching current:	Typ. 10 VAC ... 55 VAC, 25 mA Typ. 10 VDC ... 75 VDC, 15 mA

MECHANICAL CHARACTERISTIC

Terminal:	Soldering terminal
Tightening torque:	Fixing nut max. 0.5 Nm
Weight:	0.015 kg

ACOUSTICAL CHARACTERISTICS

Tone frequency:	ca. 2.0 kHz
-----------------	-------------


AMBIENT CONDITION

IP Protection:	IP40
Operating temperature:	– 25 °C ... + 55 °C
Storage temperature:	– 40 °C ... + 85 °C


CERTIFICATE

Approbations:	DNV
Conformities:	CE, UKCA, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)
REACH:	REACH compliant
RoHS:	RoHS compliant


OTHER

Short Description:	Actuator, Ø 16 mm, 24 mm x 18 mm, rectangular, Black, Plastic, Soldering terminal
Housing colour:	Black
Housing material:	Plastic
Buzzer system:	Electronic non-contacting buzzer with IC oscillator
Wiring diagrams:	

Mounting cut-outs:



Dimension drawings:



A = Solder terminal

B = Plug-in terminal 2.8 mm x 0.5 mm

Where to Buy

	Distributor	Quantity in Stock	
	element14 Singapore	18 in stock	Buy 
	Digi-Key	17 in stock	Buy 
	RS UK	17 in stock	Buy 
	Distrelec	11 in stock	Buy 
	Newark Electronics	10 in stock	Buy 

[Show more](#) 

Powered by oemsecrets.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[31-810.005](#)