

Actuator

45-
2131.4F10.000



<https://eao.com/p/45-2131.4F10.000>

Your product:



45-2131.4F10.000

Actuator

FRONT

Front dimension:	Ø 38 mm
Front form:	round
Front bezel colour:	Sand grey
Front bezel material:	Metal

MOUNTING

Design:	flush
Mounting cut-out:	Ø 30.5 mm
Mounting type:	Panel mounting

OPERATING-/INDICATION PART

Lens colour:	Black
Lens material:	Plastic
Lens illumination:	non illuminative
Lens shape:	flush
Lens optics:	opaque

MECHANICAL CHARACTERISTIC

Switching action:	Momentary
Switching system:	Slow-make switching element
Mechanical lifetime:	500 000 cycles of operation
Operating frequency:	Max. 3 600/h

Weight: 0.074 kg

AMBIENT CONDITION

IP front protection: IP66, IP67, IP69K

Operating temperature: – 25 °C ... + 70 °C

Storage temperature: – 40 °C ... + 80 °C

Shock resistance: According to IEC 60068-2-27: Sinusoidal half-wave 50 g / 11 ms

Vibration resistance: According to IEC 60068-2-6: 20 ... 500 Hz: 5 g

Climate resistance: During operation according to IEC 60721: 3K6, 3C3, 3S2, 3M6

CERTIFICATE

REACH: REACH compliant

RoHS: RoHS compliant

OTHER


Short Description: Actuator, Ø 30.5 mm, Ø 38 mm, flush, non illuminative, Black, Plastic, opaque, round, Sand grey, Metal, Momentary, IP66, IP67, IP69K

Housing colour: Silver


Housing material: Metal

Hints: Front panel thickness 1 ... 6 mm

Wiring diagrams:



Dimension drawings:



Where to Buy

Distributor		Quantity in Stock	
	Digi-Key	6 in stock	Buy 
	Mouser Electronics	1 in stock	Buy 
	Sager	0 in stock	Buy 
	Newark Electronics	0 in stock	Buy 
	RS Americas	0 in stock	Buy 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[45-2131.4F10.000](#)