

Actuator

46-
2W44.3CZ0.001



<https://eao.com/p/46-2W44.3CZ0.001>

Your product:



46-2W44.3CZ0.001 Actuator

FRONT

Front dimension:	Ø 30 mm
Front form:	round
Front bezel colour:	Silver
Front bezel material:	Metal

MOUNTING

Design:	raised
Mounting cut-out:	Ø 22.3 mm
Mounting type:	Panel mounting

OPERATING-/INDICATION PART

Lever colour:	Yellow
Lever bar colour:	Black
Lever material:	plastic
Lever shape:	short

ELECTRICAL CHARACTERISTICS

Protection class:	II
-------------------	----

MECHANICAL CHARACTERISTIC

Switching action:	Maintained - Momentary
Switching positions:	2 positions

Switching angle:	90°
Mechanical lifetime:	1 Mio. cycles of operation
Tightening torque:	2 ... 3 Nm (17.7 ... 26.6 Lb-in)
Weight:	0.038 kg


AMBIENT CONDITION

IP front protection:	IP65
IK front protection:	IK03
Operating temperature:	– 25 °C ... + 55 °C
Shock resistance:	30g, 18ms (EN-IEC 60068-2-27) 50g, 11ms (EN-IEC 60068-2-27)
Vibration resistance:	5g f= 2...500Hz (EN-IEC 60068-2-6)
Climate resistance:	+25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)


CERTIFICATE

Conformities:	CE
REACH:	REACH compliant
RoHS:	RoHS compliant
Standards:	CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508

OTHER

Short Description:	Actuator, Ø 22.3 mm, Ø 30 mm, illuminative, Yellow, short, round, Silver, Metal, Maintained - Momentary, IP65, IK03
Housing colour:	Black
Housing material:	Plastic
max. number of switching elements:	2
Switching positions:	

Dimension drawings:



Where to Buy

Distributor		Quantity in Stock		
	Distrelec	20 in stock	Buy	
	Mouser Electronics	10 in stock	Buy	
	DigiKey	5 in stock	Buy	
	TME	5 in stock	Buy	
	Farnell UK	5 in stock	Buy	

Show more +

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[46-2W44.3CZ0.001](#)