

Actuator

84-0090.7



<https://eao.com/p/84-0090.7>

Your product:



84-0090.7 Actuator

FRONT

Front dimension:	Ø 25 mm
Front form:	round
Front bezel colour:	Colourless
Front bezel material:	Plastic

MOUNTING

Design:	flush
Mounting cut-out:	Ø 22.5 mm
Mounting type:	Panel mounting

MECHANICAL CHARACTERISTIC

Tightening torque:	Fixing nut 0.8 Nm
Weight:	0.006 kg

AMBIENT CONDITION

IP front protection:	IP67
IP Protection:	IP67
Operating temperature:	– 25 °C ... + 70 °C
Storage temperature:	– 40 °C ... + 85 °C
Climate resistance:	Damp heat, cyclic: 96 hours, + 25 °C/97 %, + 55 °C/93 % relative humidity, as per EN IEC 60068-2-30 Damp heat, steady: 56 days, + 40 °C/93 % relative humidity, according to EN IEC 60068-2-78 Rapid change of temperature: 100 cycles, – 40 °C ... + 80 °C, as per EN / IEC 60068-2-14


CERTIFICATE

Approbations:	EBC (TSI PRM), NFF
Conformities:	CE, UKCA, 2011 / 65 / EC (RoHS)
REACH:	REACH compliant
RoHS:	RoHS compliant


OTHER

Short Description:	Actuator, Ø 22.5 mm, Ø 25 mm, round, Colourless, Plastic, translucent, IP67
Hints:	Front bezel illuminated
Wiring diagrams:	


Mounting cut-outs:



Dimension drawings:



A = Plug-in terminal 2.8 mm x 0.8 mm
 B = Flat ribbon cable
 E = Lens raised above bezel
 G = Lens convex raised above bezel



E = Lens raised above bezel
 G = Lens convex raised above bezel

Where to Buy

Distributor		Quantity in Stock		
	DigiKey	10 in stock	Buy	
	RS Americas	9 in stock	Buy	
	Mouser Electronics	0 in stock	Buy	
	Newark	0 in stock	Buy	
	Sager	0 in stock	Buy	

Powered by oemsecrets.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[84-0090.7](#)