

Illuminated pushbutton Ø 22 mm silver contact

82-6151.2124.B001



<https://eao.com/p/82-6151.2124.B001>

Your product:



82-6151.2124.B001
Illuminated pushbutton Ø
22 mm silver contact

FRONT

Front dimension:	Ø 25 mm
Front form:	round
Front bezel material:	Stainless steel
Front bezel shape:	flush

MOUNTING

Mounting cut-out:	Ø 22 mm
Mounting type:	Panel mounting

OPERATING-/INDICATION PART

Lens colour:	Silver
Lens material:	Stainless steel
Lens illumination:	illuminative
Lens shape:	flush
Lens optics:	opaque
Symbol:	ON/OFF
Illumination colour:	Blue
Shape of illumination:	Ring

ELECTRICAL CHARACTERISTICS

Contacts:	1 C
Operating voltage:	24 V AC/DC

Operation current:	7 mA	
Switching voltage and switching current:	according to IEC 60947-5-1 (Silver contacts) Service categorie AC-15	
	Voltage	Current
	24 VAC	1 A
	35 VAC	1 A (M12 versio
	110 VAC	1 A
	220 VAC	0.5 A
	Switch rating DC service categorie DC-13 (Silver contacts)	
	Voltage	Current
	24 VDC	0.7 A
	35 VDC	0.5 A (M12 vers
	110 VDC	0.2 A
	220 VDC	0.1 A

	according to UL 508 (Silver contacts)	
	$\cos\phi$ 0,75 ... 0,8	
	Voltage	Current
	120 VAC	5 A
	240 VAC	3 A
	24 VAC	1 A
Rated Operational Voltage Ue:	250 VAC	
Rated insulation voltage Ui:	250 V	
Electrical lifetime:	50 000 cycles of operation	
Electric strength:	1500 VAC, 50 Hz 1 minute between life terminals and ground	
Pollution degree:	2, according to EN IEC 60947-1	
Thermal current Ith:	5 A	

MECHANICAL CHARATERISTIC

Terminal:	Soldering terminal, 2.8 x 0.5 mm
Contact material:	Silver
Switching action:	Maintained
Switching system:	Snap-action switching element
Mechanical lifetime:	500 000 cycles of operation
Operating force:	4 N ... 7 N
Operating Travel:	ca. 3 mm
Tightening torque:	0.5 ... 0.6 Nm
Weight:	0.018 kg

AMBIENT CONDITION

IP front protection:	IP65, IP67
Operating temperature:	

- 40 °C ... + 80 °C

Max. 500 m / s² as per IEC 60068-2-27

10 ... 500 Hz, amplitude 1.5 mm p-p according to IEC 60068-2-6

Damp heat, 21 days according to IEC 60512-11

CERTIFICATE

CB, CCC, C UL, UL

CE, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)

REACH compliant


RoHS compliant

OTHER


Illuminated pushbutton Ø 22 mm silver contact, Maintained, 24 V AC/DC, 1 C, Soldering terminal, 2.8 x 0.5 mm, round, Stainless steel, Blue, ON/OFF, Silver

Single-LED

Wiring diagrams:



Component layouts:



Mounting cut-outs:



Dimension drawings:



A = Solder terminal
B = Screw terminal

Where to Buy

	Distributor	Quantity in Stock	
	RS UK	40 in stock	Buy 
	Distrelec	18 in stock	Buy 
	Mouser Electronics	5 in stock	Buy 
	DigiKey	5 in stock	Buy 
	Rapid Electronics	5 in stock	Buy 

Show more 

Powered by oemsecrets.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[82-6151.2124.B001](#)