

Filament lamp

10-1114.1249



<https://eao.com/p/10-1114.1249>

Your product:



10-1114.1249 Filament lamp

OPERATING-/INDICATION PART

Illumination colour: White

ELECTRICAL CHARACTERISTICS

Operating voltage: 30 V AC/DC

Operation current: 40 mA

Lumi. Intensity: mcd

MECHANICAL CHARACTERISTIC

Weight: 0.001 kg

CERTIFICATE


REACH: REACH compliant

RoHS: RoHS compliant


OTHER

Short Description: Filament lamp, T5.6, White, 30 V AC/DC

Wiring diagrams:



Dimension drawings:



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[10-1114.1249](#)