

Filament lamp

10-1319.1199



<https://eao.com/p/10-1319.1199>

Your product:



10-1319.1199

Filament lamp

OPERATING-/INDICATION PART

Illumination colour: White

ELECTRICAL CHARACTERISTICS

Operating voltage: 48 V AC/DC

Operation current: 25 mA $\pm$ 10 %

Lumi. Intensity: mcd

MECHANICAL CHARACTERISTIC

Weight: 0.001 kg

CERTIFICATE

REACH: REACH compliant

RoHS: RoHS compliant

OTHER

Short Description: Filament lamp, T1 $\frac{3}{4}$ MG, White, 48 V AC/DC

Wiring diagrams:

$x_2 +$



$x_1 -$

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[10-1319.1199](#)