

Single-LED

10-2512.1144



<https://eao.com/p/10-2512.1144>

Your product:



10-2512.1144

Single-LED

OPERATING-/INDICATION PART

Illumination colour: Yellow

ELECTRICAL CHARACTERISTICS

Operating voltage: 24 V AC/DC +10%

Operation current: 15 mA \pm 15 %

Lumi. Intensity: 300 mcd

MECHANICAL CHARATERISTIC

Weight: 0.002 kg

CERTIFICATE

REACH: REACH compliant

RoHS: RoHS compliant

OTHER

Short Description: Single-LED, BA9s, Yellow, 24 V AC/DC +10%

Kind of illumination: Single-LED

Hints: The specified 6 V DC, 24 V DC Bi-colour; 130 V AC, 130 V DC and 230 V AC versions are built with a protection diode, The specified 12, 24, 28, 48 VAC/DC versions are built with a bridge rectifier, The specified 130 VAC types are developed to run on a supply voltage of 130 VAC only, An operation at a higher supply voltage using commercial lampholders with integrated resistors, is not approved, If the 24VDC Bi-colour lamp is driven with normal polarity (plus on middle contact of the lamp) the first mentioned colour will light up, with inverted polarity the second colour will light up, The luminous intensity stated is for when used with DC, Electrical and optical data are measured at 25 °C, Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences

regarding the illumination. The customer has to decide what resistor shall be used to the LED

Wiring diagrams:













Dimension drawings:



A = (standard)
B = (super bright)

Where to Buy

	Distributor	Quantity in Stock	
	Sager	188 in stock	Buy 
	Distrelec	161 in stock	Buy 
	DigiKey	109 in stock	Buy 
	RS Americas	33 in stock	Buy 
	Mouser Electronics	14 in stock	Buy 

[Show more](#) 

Powered by oemsecrets.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[10-2512.1144](#)