


Illumination element

45-320.1J11



<https://eao.com/p/45-320.1J11>

Your product:



45-320.1J11

Illumination element

MOUNTING

Component mounting type: Front mounting

OPERATING-/INDICATION PART

Illumination colour: Blue

ELECTRICAL CHARACTERISTICS

Operating voltage: 6 - 24 V AC/DC

Surge voltage resistance: 4 kV

Lumi. Intensity: 280 - 710 mcd

MECHANICAL CHARACTERISTIC

Terminal: Screw terminal

Weight: 0.008 kg

CERTIFICATE


REACH: REACH compliant

RoHS: RoHS compliant


OTHER

Short Description: Illumination element, Screw terminal, Blue, 6 - 24 V AC/DC, Front mounting











Wiring diagrams:



Dimension drawings:



Where to Buy

Distributor		Quantity in Stock		
	Digi-Key	28 in stock	Buy	
	Mouser Electronics	1 in stock	Buy	
	RS Americas	0 in stock	Buy	
	Newark Electronics	0 in stock	Buy	
	Sager	0 in stock	Buy	

Powered by oemsecrets.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[45-320.1J11](#)