

q

Basket

Your basket is empty.

Produktkonfiguration

Product is incomplete


704.064.2
Emergency-stop switch
actuator, foolproof EN
IEC 60947-5-5

Save

704.064.2 - Emergency-stop switch actuator, foolproof EN IEC 60947-5-5



Attention: The preview is based on a sample product. This can differ from your current configuration.



Specification

Mounting

Mounting cut-out
Design

Ø 22.5 mm
raised

Front

Front shape
Front dimension

round
Ø 37 mm

Other Attributes

Marking
Weight

Arrows
0.300 kg

Operating-/Indication part

Lens material
Lens optics
Lens profile
Lens colour

Plastic
opaque
Mushroom
red

IP-Rating

Front protection

IP 65

Actuator

Switching action

Maintained

Function

Emergency stop switch

Legend

Switching action: C = Maintained

Select Necessary Components



Actuator



Bayonet flange



Switching element

Select Optional Accessories

Additional Information

- Shaft yellow
- Twist to unlock anti-clockwise
- Max. 3 slow-make elements can be clipped on
- Application as per DIN EN ISO 13850 and EN 60204-1

Information For Download

Create datasheet

Dimensions (eps, 460.6 kB)

Mounting cut-outs (eps, 682.5 kB)

Wiring diagram (eps, 177.3 kB)

Tech. Data Serie.pdf (451.5 kB)

3D Data

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EAO:

704.064.2