

# EAO – Your Expert Partner for Human Machine Interfaces

## 82-5151.0114 - Indicator 19 mm stainless-steel

### 82-5151.0114 - Indicator 19 mm stainless-steel



*Attention: The preview is based on a sample product. This can differ from your current configuration.*

#### Mounting

Mounting cut-out	Ø 19 mm
Design	flush

#### Front

Front dimension	Ø 22 mm
Front shape	round
Front ring shape	flush
Front bezel material	Stainless steel

#### Other Attributes

Operating voltage	24 V AC/DC
Weight	0,018 kg
Operation current	7 mA

#### Operating-/Indication part

Lens optics	opaque
Lens material	Stainless steel
Lens profile	flat
Lens illumination	illuminative
Lens colour	Stainless steel

#### IP-Rating

Front protection	IP65, IP67
------------------	------------

#### Connection Method

Terminal	Solder 2.8 x 0.5 mm
----------	---------------------

#### Illumination

Illumination	Ring with red LED
--------------	-------------------


#### Function

Indicator
-----------


# EAO – Your Expert Partner for Human Machine Interfaces

82-5151.0114 - Indicator 19 mm stainless-steel


## Dimensions




## Mounting cut-outs



## Wiring diagram



## Component layout



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EAO:

[82-5151.0114](#)