



TYT SERIES

HIGH PERFORMANCE 3-PHASE, 4-WIRE FILTERS

COMPONENTS

PART NO.	Cx(μF)	Cx1(μF)	Cy(nF)	L(mH)	R(KΩ)	R1(KΩ)
16TYT8	0.68	1.0	15.0	1.2	220	-
25TYT8	2.0	2.0		1.3	100	
36TYT8				0.95		
50TYT8				0.55		
100TYT8	2.0	2.0	47.0	0.32	330	680
150TYS10	6.6	6.6	470	0.11		


INTRODUCTIONS

1. Applications: Electric equipment, UPS, machine tool, copy machine, automation equipment, robot, AC motor drive
2. Voltage rating: 480VAC
3. Operating frequency: 50/60Hz

MINIMUM INSERTION LOSS IN dB

COMMON MODE (L-G) IN 50 OHM SYSTEM						
PART NO.	FREQUENCY-MHz					
	.15	.50	1.0	5.0	10	30
16TYT8	25	50	50	50	45	30
25TYT8	25	50	50	50	45	30
36TYT8	25	50	50	50	40	25
50TYT8	25	45	45	40	40	25
100TYT8	10	20	25	30	30	20
150TYS10	10	20	25	30	30	20
DIFFERENTIAL MODE (L-L) IN 50 OHM SYSTEM						
16TYT8	35	55	60	60	40	30
25TYT8	35	55	60	60	40	30
36TYT8	30	50	55	50	40	30
50TYT8	30	50	50	40	40	30
100TYT8	30	40	40	35	35	25
150TYS10	30	40	40	35	35	35

ELECTRICAL SCHEMATIC






R1 : 680KΩ , FOR 150TYS10 ONLY

SERIES DIMENSIONS

PART NO.	DIMENSIONS IN INCHES/mm						
	A	B	C	D	E	F	G
16TYT8	5.591 142.0	4.213 107.0	3.228 82.0	7.539 191.5	6.516 165.5	196.9 50.0	7.559 192.0
25TYT8							
36TYT8							
50TYT8	5.689 144.5	4.882 124.0	4.094 104.0	7.638 194.0	6.614 168.0	3.858 98.0	7.638 194.0
100TYT8	8.346	6.378	5.197	9.921	9.134	4.724	11.496
*150TYS10	212.0	62.0	132.0	252.0	232.0	120.0	292.0

*Screw type

MECHANICAL CONSTRUCTION



UNIT: INCH
mm



TYT SERIES

HIGH PERFORMANCE 3-PHASE 4-WIRE FILTERS




INTRODUCTIONS

1. Applications: Electric equipment, UPS, machine tool, copy machine, automation equipment, robot, AC motor drive
2. Voltage rating: 520VAC
3. Operating frequency: 50/60Hz

COMPONENTS

PARTNO.	L(mH)	Cx(uF)	Cy(uF)	R1 (Ω)	R2 (KΩ)
08TYT8-1	2.4	2.2	0.1	1.5M	680
16TYT8-1	1.7				
25TYT8-1	1.6				
36TYT8-1	1.0				
64TYT8-1	0.7	4.7	0.147	330K	680
80TYT8-1	0.55				
120TYT8-1	0.55				
160TYT8-1	0.5				



ELECTRICAL SCHEMATIC



SERIES DIMENSIONS

PART NO.	DIMENSIONS IN INCHES/mm									
	A	B	C	D	E	F	G	H	I	J
08TYT8-1	4.33	0.45	3.15	3.72	4.33	2.76	0.98 25.0	0.47	3.23	M6
16TYT8-1	110.0	11.5	80.0	94.5	110.0	70.0		12.0	82.0	M10
25TYT8-1	5.12	0.96	3.54	4.02	4.65	3.35		0.55	3.54	
36TYT8-1	130.0	24.5	90.0	102.0	118.0	85.0		14.0	90.0	
64TYT8-1	5.51	1.52	3.94	5.02	5.63	4.53	1.57	0.71	4.53	
	140.0	38.5	100.0	127.5	143.0	115.0	40.0		115.0	
80TYT8-1	6.69	1.69	4.72	5.81	6.42	4.92	1.38	18.0	5.31	
	170.0		120.0	147.5	163.0		35.0		135.0	
120TYT8-1	8.27	43.0	6.3	6.04	6.69	125.0	1.73	0.69	5.51	
	210.0		160.0	153.5	170.0		44.0	17.5	140.0	
160TYT8-1	7.87	1.95	5.91	6.81	7.48	5.12	2.17	0.65	6.3	
	200.0	49.5	150.0	173.0	190.0	130.0	55.0	16.5	160.0	

MECHANICAL CONSTRUCTION





TYT SERIES

HIGH PERFORMANCE 2-STAGE 3-PHASE 4-WIRE FILTERS




INTRODUCTIONS

1. Applications: Electric equipment, UPS, machine tool, copy machine, automation equipment, robot, AC motor drive
2. Voltage rating: 520VAC
3. Operating frequency: 50/60Hz

COMPONENTS

PARTNO.	L1(mH)	L2(uH)	Cx(uF)	Cy(uF)	R1(M Ω)	R2(KΩ)
08TYT8-2	2.4	7.0	3.3	3.4	1.5	660.0
16TYT8-2	1.7					
25TYT8-2	1.6	6.0	4.7			
36TYT8-2	1.0					
64TYT8-2	0.7	7.0	9.4			
80TYT8-2	0.55					
120TYT8-2	0.55	6.0	13.6			
160TYT8-2	0.5					



ELECTRICAL SCHEMATIC



SERIES DIMENSIONS

PART NO.	DIMENSIONS IN INCHES/mm									
	A	B	C	D	E	F	G	H	I	J
08TYT8-2	4.72	0.45	3.15	5.02	5.63	1.3	3.15	0.51 13.0	4.53	M6
16TYT8-2	120.0	11.5	80.0	127.5	143.0	33.0	80.0		115.0	
25TYT8-2	5.12	0.98	3.54	5.41 137.5	6.02 153.0	1.97	4.53		4.92 125.0	
36TYT8-2	130.0	25.0	90.0			50.0	115.0			
64TYT8-2	6.3 160.0	1.54 39.0	3.94 100.0			2.17 55.0	4.92	0.77		5.31 135.0
80TYT8-2	9.06 230.0	1.73	4.72 120.0	5.81 147.5	6.42 163.0	1.77 45.0			125.0	
120TYT8-2	9.84 250.0		44.0	7.87 200.0	6.04 153.5	6.69 170.0	2.17 55.0	5.51 140.0	0.75	5.51
160TYT8-2	11.02 280.0	2.0 50.7	9.06 230.0	1.97 50.0			6.69 170.0	19.0	140.0	

MECHANICAL CONSTRUCTION



UNIT: INCH
mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Delta Electronics:

[08TYT8-1](#) [08TYT8-2](#) [100TYT8](#) [120TYT8-1](#) [120TYT8-2](#) [150TYS10](#) [160TYT8-1](#) [160TYT8-2](#) [16TYT8](#) [16TYT8-1](#)
[16TYT8-2](#) [25TYT8](#) [25TYT8-1](#) [25TYT8-2](#) [36TYT8](#) [36TYT8-1](#) [36TYT8-2](#) [50TYT8](#) [64TYT8-1](#) [64TYT8-2](#) [80TYT8-1](#)
[80TYT8-2](#) [100TYT2](#)