

AMI400-9

Expandable Type for IBASE MI910 Mini-ITX Motherboard

Fanless System



Features

- Fanless system with IBASE MI910E Mini-ITX motherboard
- One expansion slot outlet on rear panel
- Available in silver color
- One 2.5" HDD drive bay
- One expandable PCI slot
- Fanless operation
- Wall mount kit included

Specifications

System Mainboard	MI910E
CPU Type	Intel® Core™2 Duo T7500
System Speed	2.2GHz
Memory	2x DDR2 DIMM, Max. 2GB
Construction	Aluminum & Steel
Chassis Color	Silver (Aluminum)
Front Panel External I/O	Power LED, HDD LED, Reset button power on/off button, 2x USB 2.0 ports
Rear Panel External I/O	Audio, 1x LAN, 4x USB, COM, VGA, SPDIF, 1394, KB/MS
Storage	1x 2.5" HDD drive bay
Expansion Slot	1x PCI
Power Supply	150W power adaptor
Mounting	Desktop or wall mount (wall mount kit included)
Dimensions	226mm(W) x 263.5mm(D) x 109mm(H)
Operating Temperature	0°C~ 45°C (32°F~113°F)
Storage Temperature	-20°C~80°C (-4°F~176°F)
Relative Humidity	5~90% @ 45°C, (non-condensing)
Vibration	CFD: 5 grms/5~500Hz random operation HDD: 0.25 grms/5~500Hz random operation

Ordering Information

AMI400-9	Aluminum System with MI910E, Intel® T7500 (2.2GHz) CPU, 2GB DDR2, 2.5" 320GB HDD, ID392 DVI board, IP115 PCI riser card, 110W DC-DC converter, 150W power adaptor
AMI400-9C	Aluminum Chassis for MI910E, 2.5" HDD holder, 110W DC-DC converter, 150W power adaptor, IP115 PCI riser card

AMI400-8

Slim Type for IBASE MB899 Mini-ITX Motherboard

Fanless System



Features

- Mini-ITX system with IBASE MB899HF Mini-ITX motherboards
- Chassis with Intel® Celeron® 440 processor, 1.83GHz
- Available in silver color
- One 2.5" HDD drive bay
- Fanless operation
- Wall mount kit included

Specifications

System Mainboard	MB899HF
CPU Type	Intel® Celeron® 440
System Speed	1.83GHz
Memory	2x DDR2 DIMM, Max. 2GB
Construction	Aluminum & Steel
Chassis Color	Silver (Aluminum)
Front Panel External I/O	Power LED, HDD LED, Reset button power on/off button, 2x USB 2.0 ports
Rear Panel External I/O	Audio, 2x LAN, 4x USB, COM, VGA, TV out, SPDIF, 1394, KB/MS
Storage	1x 2.5" HDD drive bay
Expansion Slot	1x PCI
Power Supply	150W power adaptor
Mounting	Desktop or wall mount (wall mount kit included)
Dimensions	226mm(W) x 263.5mm(D) x 109mm(H)
Operating Temperature	0°C~ 45°C (32°F~113°F)
Storage Temperature	-20°C~80°C (-4°F~176°F)
Relative Humidity	5~90% @ 45°C, (non-condensing)
Vibration	CFD: 5 grms/5~500Hz random operation HDD: 0.25 grms/5~500Hz random operation

Ordering Information

AMI400-8	Aluminum System with MB899HF, Intel® 440 (1.83GHz) CPU, 1GB DDR2, 2.5" 320GB HDD, IP115 PCI riser card, 110W DC-DC converter, 150W power adaptor
AMI400-8C	Aluminum Chassis for MB899HF, 2.5" HDD holder, 110W DC-DC converter, 150W power adaptor, IP115 PCI riser card



01
Motherboards

02
Disk-Size SBCs

03
CPU Modules

04
PC 104 Plus

05
CPU Cards

06
RISC SBCs

07
Embedded Systems

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IBASE:](#)

[SYS-AMI400-8](#) [SYS-AMI400-9](#) [AMI400-8](#) [AMI400-9](#)