



NEW



Features

- AMD Ryzen™ Embedded V1000/R1000 on board
- 2x DDR4 SO-DIMM, Max. 32GB
- 2x PCI-E Gigabit LAN
- 2x HDMI, 1x eDP, 1x 24-bit LVDS dual-channel
- 1x USB2.0, 4x USB3.1, 1x SATA III, 4x COM
- 2x M.2 sockets (M/ E key)




Specifications

CPU	AMD Ryzen™ Embedded V1000/R1000 on board
PCH	N/A
Memory Types	DDR4-2400 SO-DIMM, Max. 32GB, supports ECC
BIOS	AMI
Watchdog Timer	256 levels
H/W Monitor	Yes
Storage Device Interface	1x M.2 (M-Key)
Mini Type Slots	1x M.2 (M-key, type:2280, NVMe) 1x M.2 (E-key, type:2230, CNVi)
Graphics Controller	AMD Raden™ Vega integrated
Video Output	2x HDMI(2.0a), 1x 24-bit dual channel LVDS & eDP
Ethernet	2x Intel® I211AT PCI-E Gigabit LAN
I/O Chip	Fintek F81964D-I
Serial Port	1x RS232/422/485 (Jumperless selection) 3x RS232
USB 2.0	1x USB2.0 on board
USB 3.0/ 3.1	4x USB3.1 on board
Serial ATA	1x SATA III
Audio	Built-in audio w/ Realtek ALC269Q-VC3-GR, w/ class-D amplifier
TPM	N/A
Others	Digital I/O(4-in/ 4-out), EuP/ErP, +12V~+24V DC-in (+/-10%)
Dimensions (L x W)	102mm x 147mm (4" x 5.8")
Power Consumption	TBD
Operating Temperature	0°C~60°C (32°F~140°F)
Storage Temperature	-20°C~80°C (-4°F~176°F)
Relative Humidity	90% (non-condensing@60°C)

Ordering Information

IB918F-1605 Art. N° 159026	AMD Ryzen™ V1605B QC APU (2.0GHz~3.6GHz) on board 3.5-inch Disk-Size w/ dual LAN, 2x HDMI, eDP & LVDS (24-bit dual-channel), EuP/ErP, 12V~24V DC-in
IB918F-1202 Art. N° 159027	AMD Ryzen V1202B DC APU (2.3GHz~3.3GHz) on board 3.5-inch Disk-Size w/ dual LAN, 2x HDMI, eDP & LVDS (24-bit dual-channel), EuP/ErP, 12V~24V DC-in

Dimensions and Drawing



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IBASE:](#)

[HSIB918-1](#) [HSIB918-A](#) [IB918F-1202](#) [IB918F-1505G](#) [IB918F-1605](#) [IB918F-1606G](#)