


Features

- AMD Ryzen™ Embedded V2000 on board
- 2x DDR4 SO-DIMM, Max. 64GB
- 2x Gigabit LAN
- Supports 2x DisplayPort (DP connector and Type-C), 1x eDP, 1x 24-bit dual-channel LVDS
- 2x USB 2.0, 3x USB 3.1, 2x SATA III, 2x COM
- 2x M.2 sockets (M-Key/ E-Key)


Specifications

CPU	AMD Ryzen™ Embedded V2000 on board
PCH	N/A
Memory	DDR4-3200 SO-DIMM, Max. 64GB, supports ECC
BIOS	AMI
Watchdog Timer	256 levels
H/W Monitor	Yes
Storage Device Interface	1x M.2 (M-Key)
Mini Type Slots	1x M.2 (M-Key, type:2280, NVMe) 1x M.2 (E-Key, type:2230)
Graphics Controller	AMD Raden™ Vega integrated
Video Output	2x DisplayPort (DP connector & Type-C), 1x 24-bit dual-channel LVDS, 1x eDP
Ethernet	2x Intel® I211AT or I210AT Gigabit LAN
I/O Chipset	Fintek F81964
Serial Port	1x RS232/422/485 (Jumperless selection) 1x RS232
USB 2.0	2x USB 2.0 on board
USB 3.X	3x USB 3.1 on board
Serial ATA	2x SATA III
Audio	Built-in audio w/ Realtek ALC888S
TPM	TPM (2.0)
Others	Digital I/O(4-in/ 4-out), EuP/ErP, +12V~+24V DC-in (+/-10%)
Dimensions (L x W)	102mm x 147mm (4" x 5.8")
Power Consumption	AMD Ryzen™ Embedded V2748 2.9GHz w/ 2x 16GB DDR4-3200 +12V: 7.61A AMD Ryzen™ Embedded V2718 1.70GHz w/ 2x 16GB DDR4-3200 +12V: 3.92A
Operating Temperature	0°C~60°C (32°F~140°F)
Storage Temperature	-20°C~80°C (-4°F~176°F)
Relative Humidity	95% (non-condensing@60°C)

Ordering Information

IB952F-2748	AMD Ryzen™ V2748 Octa APU (2.9GHz~4.15GHz) on board 3.5" SBC w/ dual LAN, 2x DisplayPort (DP+ Type-C), eDP & LVDS (24-bit dual-channel), EuP/ErP, 12V~24V DC-in
IB952F-2718	AMD Ryzen™ V2718 Octa APU (1.7GHz~4.15GHz) on board 3.5" SBC w/ dual LAN, 2x DisplayPort (DP+ Type-C), eDP & LVDS (24-bit dual-channel), EuP/ErP, 12V~24V DC-in
HSIB952-A	Heatsink with Fan for IB952F-2718
HSIB952-B	Heatsink with Fan for IB952F-2748
HSIB952-1	Heat spreader for IB952
IB92	Cable kit w/ COM, Power, SATA + Power

Dimensions and Drawing



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IBASE:](#)

[IB952F-2718](#) [IB952F-2748](#)