

Microsoft® Wired Desktop 600



Name Information	
Product Name	Microsoft® Wired Desktop 600
Keyboard Name	Microsoft Wired Keyboard 600
Mouse Name	Microsoft Basic Optical Mouse v2.0
Product Dimensions	
Keyboard Length	17.9 inches (456 millimeters)
Keyboard Width	6.28 inches (160 millimeters)
Keyboard Depth/Height	1.68 inches (42.7 millimeters) with tilt legs extended
Keyboard Weight	20.1 ounces (595 grams)
Keyboard Cable Length	78.7 inches (2000 millimeters)
Mouse Length	4.47 inches (113 millimeters)
Mouse Width	2.28 inches (57.9 millimeters)
Mouse Depth/Height	1.54 inches (39.2 millimeters)
Mouse Weight	3.27 ounces (92.8 grams)
Mouse Cable Length	72 +6/-0 inches (1830 +150/-0 millimeters)
Compatibility and Localization	
Interface	<ul style="list-style-type: none"> • Keyboard: USB compatible • Mouse: USB compatible
Operating Systems	<ul style="list-style-type: none"> • Microsoft Windows® 10 / 8.1 / 8 / RT¹ 8.1 / RT 8, and Windows 7 • Macintosh Mac OS X v10.7x- 10.10 • Android 3.2 – 5.0 <p>¹Advanced functionality not available with all devices. See compatibility information at: microsoft.com/hardware/compatibility</p>
Top-line System Requirements	<p>For a Microsoft Windows-based PC: Requires a PC that meets the requirements for and has installed one of these operating systems:</p> <ul style="list-style-type: none"> • Windows 10 / 8.1 / 8 / RT 8.1 / RT 8, and Windows 7 • 150 MB • USB <p>For a Macintosh PC:</p> <ul style="list-style-type: none"> • Macintosh Mac OS X v10.7x-10.10 • USB port
Compatibility Logos	<ul style="list-style-type: none"> • Compatible with Microsoft Windows 10 / 8 / Windows RT / 7 • Mac logo • Universal Mac logo
Software Localization	No software required
Keyboard Localization	<p>Available language sets will vary by product and sales channel.</p> <p>104 key configuration: Arabic, Chinese (Simplified), Chinese (Traditional), English (Canada), English (North America), Greek, International English (EURO), International English (ROW), Polish/Romanian, Russian, and Thai</p> <p>105 key configuration: English (UK), French (Canada), French (France), German (Germany), Hungarian, Spanish (Latin America), and Turkish</p> <p>106 key configuration: Korean</p> <p>107 key configuration: Brazilian (Portuguese)</p> <p>109 key configuration: Japanese</p>
Tracking Technology	
Mouse Tracking System	Optical tracking system
Imaging Rate	Up to 3000 frames per second
X-Y Resolution	800 points per inch (31.5 points per millimeter)
Tracking Speed	Up to 20 inches (508 millimeters) per second
Product Feature Performance	
QWERTY Key Life	20,000,000 actuations per key
Hot Key Features	Windows 8 Charms keys, Windows Start key, and Calculator
Hot Key Life	500,000 actuations per key
Multimedia Key Features	Play/Pause, Volume +, Volume -, and Mute
Multimedia Key Life	30,000 actuations per key
Typing Speed	1000 characters per minute
Mouse Button Features	3 buttons including scroll wheel button
Right & Left Button Life	3,000,000 actuations
Wheel Button Life	250,000 actuations
Mouse Scrolling Features	Standard vertical scroll wheel
Wheel Vertical Scrolling Life	<ul style="list-style-type: none"> • 100,000 revolutions (away from user) at no more than 60 rotations per minute • 300,000 revolutions (toward user) at no more than 60 rotations per minute
Storage Temperature & Humidity	-40°F (-40°C) to 140°F (60°C) at 5% to 65% relative humidity (non-condensing)
Operating Temperature & Humidity	32°F (0°C) to 104°F (40°C) at 5% to 80% relative humidity (non-condensing)
Certification Information	
Country of Manufacture	People's Republic of China (PRC)
ISO 9001 Qualified Manufacturer	Yes
ISO 14001 Qualified Manufacturer	Yes
Restriction on Hazardous Substances	This device complies with all applicable worldwide regulations and restrictions including, but not limited to: EU directive 2002/95/EC on the Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment and EU Registration Evaluation and Authorization of Chemicals (REACH) regulation regarding Substances of Very High Concern.
FCC ID	This device complies with part 15 of the FCC Rules and Industry Canada ICES-003. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Tested to comply with FCC standards. For home and office use. Model numbers: 1576, Wired Keyboard 600 and 1113, Basic Optical Mouse v2.0.
Certification Information	
Agency and Regulatory Marks	<ul style="list-style-type: none"> • ACA/MED Declaration of Conformity (Australia and New Zealand) • ICES-003 report on file (Canada) • EIP Pollution Control Mark, EPUP (China) • CE Declaration of Conformity (European Union) • WEEE (European Union) • VCCI Certificate (Japan) • KCC Certificate (Korea) • EAC Certificate (Russia, Kazakhstan) • BSMI DoC (Taiwan) • FCC Declaration of Conformity (USA) • CB Scheme Certificate (International)
Warranty	3 years
Windows Certification Kit (WCK)	Bundle ID: 1731370 (32-bit) and (64-bit) Windows 10, 1608482 (32-bit) and 1612257 (64-bit) Windows 8.1

Results stated herein are based on internal Microsoft testing. Individual results and performance may vary. Any device images shown are not actual size. This document is provided for informational purposes only and is subject to change without notice. Microsoft makes no warranty, express or implied, with this document or the information contained herein. Review any public use or publications of any data herein with your local legal counsel.

©2016 Microsoft Corporation. The names of actual companies and products mentioned herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[96KB-104U-MS-US-B](#)