

96PR-102-UB3-M

203 dpi Mobile Barcode Printer, 3", 4 ips, USB/Bluetooth



Features

- 3" mobile barcode receipt printer
- Resolution: 203 dpi
- Max. print speed: 102mm (4")/sec
- USB, Bluetooth
- 4 MB Flash memory and 8 MB SDRAM memory

Specifications

Resolution	8 dots/mm (203 dpi)
Printing method	Direct Thermal
Max. print speed	102 mm (4")/second
Max. print width	72 mm (2.83")
Max. print length	2,286 mm (90")
Enclosure	Plastic with rubber over-mold construction
Physical dimension (W x H x D)	116 x 148 x 70 mm (4.57" x 5.83" x 2.75")
Weight (including battery)	0.55 kg (1.212 lbs)
Drop specification	1.5 m (5 ft)
IP rating	IP54 (w/case)
Max. roll capacity	Receipt: 57 mm (2.25") OD Label: 55 mm (2.16") OD
Processor	32-bit RISC CPU
Memory	• 4 MB Flash memory • 8 MB SDRAM
Interface	• USB 2.0 • Bluetooth • 802.11 b/g/n Wireless (option) • RS-232 (option)
Power	Two-cell, 7.4V _{DC} , 2500 mAh Li-ion rechargeable battery
Operation switch, button	• 3 buttons (On/off, feed, and cover-open) • 2 color LED for printer status, 3 LEDs for battery status
Sensors	• Reflective sensor • Head open sensor
Internal fonts	• 8 alpha-numeric bitmap fonts • One Monotype Imaging® CG Triumvirate Bold Condensed scalable font
Bar code	• 1D bar code Code 39, Code 93, Code128UCC, Code128 subsets A,B,C, Codabar, Interleave 2 of 5, EAN-8, EAN-13, EAN-128, UPC-A, UPC-E, EAN and UPC 2(5) digits add-on, MSI, PLESSEY, POSTNET, China POST, GS1 Data bar • 2D bar code PDF-417, Maxicode, DataMatrix, QR code, Aztec
Printer language	TSPL-EZTM (Compatible to EPL, ZPL, ZPL II) or CPCL emulation
Media type	Receipt paper, Bline receipt paper (Black mark in printing side) & Selected label
Media width	Receipt: 50.8 ~ 80 mm (2" ~ 3.15") Label: 50.8 ~ 78 mm (2" ~ 3.07")
Media thickness	Receipt: 0.0508 ~ 0.1016 mm (2 ~ 4 mil) Label: Fasson standard label media up to 0.14 mm (5.5 mil)
Media height	Label: Min. 25.4 mm (1")
Media core diameter	10.2 ~ 25.4 mm (0.4" ~ 1")
Environment condition	Operation: -10 ~ 50 °C (14 ~ 122 °F), 10 ~ 90% non-condensing Storage: -40 ~ 60 °C (-40 ~ 140 °F), 10 ~ 90% non-condensing
Safety regulation	FCC, CE, CB, CCC, C-Tick
Environmental concern	Comply with RoHS, WEEE
Accessories	• Windows labeling software CD disk • Belt Clip • Power adapter • Quick start guide • Li-ion battery
Options	• 802.11 b/g/n Wireless network • USB to RS-232 converter cable • Li-ion battery • Vehicle power adapter • Bluetooth module • USB cable • Charge station 1 cell (with changeable power connector) • IP54-rated protective case with shoulder strap

Ordering Information

Part Number	Description
96PR-102-UB3-M	Mobile Barcode Printer, 203dpi, 3", 4 ips, USB/Bluetooth, US power cord
96PR-102-UB3-M-E	Mobile Barcode Printer, 203dpi, 3", 4 ips, USB/Bluetooth, EU power cord

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[96PR-102-UB3-M](#)