

96PR-127-UB-D

300 dpi Desktop Barcode Printer, 4.16",
5 ips, USB/Bluetooth



Features

- 4" desktop barcode label printer
- Resolution: 300 dpi
- Max. print speed: 127mm (5")/sec
- USB, Bluetooth

Specifications

Resolution	12 dots/mm (300 dpi)
Printing method	Thermal Transfer & Direct Thermal
Max. print speed	127 mm (5")/second
Max. print width	105.6 mm (4.16")
Max. print length	1,016 mm (40")
Enclosure	ABS plastic
Physical dimension (W x H x D)	204 x 164 x 280 mm (8.03" x 6.46" x 11.02")
Weight	2.4 kg (5.29 lbs)
Label roll capacity	127 mm (5") OD
Ribbon	300 m long, max. OD 67 mm, 1" core (ink coated outside), 110 m long, max. OD 40 mm, 0.5" core (ink coated outside)
Ribbon width	40 mm ~ 110 mm (1.6" ~ 4.3")
Processor	32-bit RISC CPU
Memory	• 8 MB Flash memory • 16 MB SDRAM
Interface	• USB 2.0 • Internal Bluetooth 4.0
Power	External universal switching power supply • Input: AC 100-240V, 2.5A, 50-60Hz • Output: DC 24V, 2.5A, 60W
Operation switch, button LED	1 power switch, 1 feed and pause button & 1 LED (3 colors: green, amber & red)
Sensors	• Transmissive gap sensor • Ribbon end sensor • Black mark reflective sensor (position adjustable) • Head open sensor
Internal fonts	• 8 alpha-numeric bitmap fonts • Monotype Image® true type font engine with one CG Triumvirate Bold Condensed scalable font
Bar code	• 1D bar code - Code 128UCC, Code 128 subsets A, B, C, EAN128, Interleaved 2 of 5, Interleaved 2 of 5 with check digit, Code 39, Code 39 with check digit, Code 93, EAN13, EAN8, UPCA, UPCE, EAN and UPC 2 (5) digits add-on, Codabar, Postnet, MSI, MSI with check digit, PLESSEY, China post, ITF14, Code 11, TELEPEN, TELEPEN, PLANET, Code49, Deutsche Post Identcode, Deutsche Post Leitcode, LOGMARS • 2D bar code - GS1 DataBar, GS1 DataMatrix, Maxicode, AZTEC, PDF417, QR Code, Micro PDF 417
Font and barcode rotation	0, 90, 180, 270 degree
Printer language	TSPL-EZTM (Compatible to EPL, ZPL, ZPL II)
Media type	Continuous, die-cut, black mark, fan-fold, notched (outside wound)
Media width	20 ~ 112 mm (0.8" ~ 4.4")
Media thickness	0.06 ~ 0.19 mm (2.36 ~ 7.48 mil)
Media core diameter	25.4 ~ 38 mm (1" ~ 1.5")
Label length	10 ~ 1,016 mm (0.39" ~ 40")
Environment condition	Operation: 5 ~ 40°C, 25 ~ 85% non-condensing Storage: -40 ~ 60°C, 10 ~ 90% non-condensing
Safety regulation	FCC Class A, CE Class A, C-Tick Class A, UL, cUL, TÜV/safety, CCC, EAC, CoC, BIS, KC, Energy StarR
Environmental concern	Comply with RoHS, REACH, WEEE
Accessories	• Quick start guide • Power cord • 1" label spindle, fixing tab x 2, 1.5" adapter x 2 • 1" ribbon paper core • USB cable • External universal switching power supply • 1" ribbon spindle x 2 for 300 m ribbon

Ordering Information

Part Number	Description
96PR-127-UB-D	Desktop Barcode Printer, 300dpi, 4.16", 5 ips, USB/Bluetooth, US power cord
96PR-127-UB-D-E	Desktop Barcode Printer, 300dpi, 4.16", 5 ips, USB/Bluetooth, EU power cord

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[96PR-127-UB-D](#)