

96PS-A100WFX-1

ATX Power Supply



<http://www.advantech.com/certified-peripherals/>

Features

- Widely input range from 90 to 264 VAC
- Low ripple & noise
- MTBF:100K hours at 25°C, and well working performance at 50°C
- Support OTP, OVP and OLP circuit protection
- Common safety for CB, CE, TUV, UL, FCC, and CCC

General

Advantech Part Number	96PS-A100WFX-1
Description	FSP AC to DC 90-264V 100W W/PFC Switch Power Supply FLEX ATX
Manufacturer	FSP Technology

Output Specifications

Output Power	100W
Output Voltage & Current	+5V @ 8A;+12V @ 4A;12V @ 0.3A;+5Vsb @ 2A;+3.3V @ 6A
Efficiency (%)	0.7
Main Connector	ATX (7 pin)

Mechanical

Form Factor	FLEX
Dimension (L x W x H)	150×81.5×40.5mm
Vibration	0.5g
MTBF	100K
Fan Function	Yes
Power Switch Function	Yes

Input Specifications

Input Voltage Range	90 - 264V
Input Current	3A @115Vac;1.5A @230Vac
Input Frequency	47 - 63Hz
PFC Function	W/PFC
Input Current Type	AC to DC

Environmental Specification

Storage Temp.	-20 - 80°C
Storage Humidity	0.95
Operating Temp. (°C)	0 50°C

Safety

Safety & EMC	Class B
Max Temp. (°C) @ Load	25C@100%
Safety Standard	UL/ CB / CCC / CE / FCC / TUV
RoHs	Yes

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[96PS-A100WFX-1](#)