

ADAM-4510I ADAM-4520I ADAM-4117

Robust RS-422/485 Repeater

Robust RS-232 to RS-422/485 Converter Robust 8-ch Analog Input Module with Modbus



ADAM-4510I



ADAM-4520I



ADAM-4117



Specifications

General

- **Connectors** 2 x plug-in terminal blocks (#14 ~ 22 AWG)
- **Power Consumption** 1.4 W @ 24 V_{DC}
- **Certification** FCC, CE, UL, UL C1D2

Communications

- **Input** RS-485 (2-wire) or RS-422 (4-wire)
- **Output** RS-485 (2-wire) or RS-422 (4-wire)
- **Speed Modes (bps)** 1,200, 2,400, 4,800, 9,600, 19.2 k, 38.4 k, 57.6 k, 115.2 k, RTS control and RS-422 (switchable)
- **Supports Auto Baud-Rate**
- **Provide RS-485 to RS-422 Convert Ability**

Specifications

General

- **Connectors** 1 x plug-in terminal block (#14 ~ 22 AWG) (RS-422/485)
1 x DB9-F (RS-232)
- **Power Consumption** 1.2 W @ 24 V_{DC}
- **Certification** FCC, CE, UL, UL C1D2

Communications

- **Input** RS-232 (DB9)
- **Output** RS-485 (2-wire) or RS-422 (4-wire)
- **Speed Modes (bps)** 1,200, 2,400, 4,800, 9,600, 19.2 k, 38.4 k, 57.6 k, 115.2 k, RTS control and RS-422 (switchable)
- **Supports Auto Baud-Rate**

Specifications

General

- **Connectors** 2 x plug-in terminal blocks (#14 ~ 22 AWG)
- **Watchdog Timer** System (1.6 second) & Communication
- **Supported Protocols** ASCII Command and Modbus/RTU
- **Power Consumption** 1.2 W @ 24 V_{DC}
- **Interface (B version)** RS-485, micro USB
- **Certification** FCC, CE

Analog Input

- **Channels** 8 differential and independent configuration channels
- **Input Impedance** 20 MΩ
- **Input Type** mV, V, mA
- **Input Range** 0 ~ 150mV, 0 ~ 500mV, 0 ~ 1V, 0 ~ 5V, 0 ~ 10V, 0 ~ 15V, ±150 mV, ±500 mV, ±1V, ±5 V, ±10 V, ±15V, ±20 mA, 0 ~ 20 mA, 4 ~ 20mA
- **Accuracy** Voltage mode : ±0.1% or better
Current mode : ±0.2% or better
- **Resolution** 16-bit
- **Sampling Rate** 10/100 samples/sec (selected by utility)
- **CMR @ 50/60 Hz** 92 dB
- **Over Voltage Protection** ±60 V_{DC}
- **High Common Mode** 200 V_{DC}
- **Span Drift** ±25 ppm/°C (Typical)
- **Zero Drift** ±6μV/°C
- **Built-in TVS/ESD Protection**

Common Specifications

General

- **Power Input** Unregulated 10 ~ 48 V_{DC} w/power reversal protection
- **Isolation Voltage** 3,000 V_{DC}

Environment

- **Operating Humidity** 5 ~ 95% RH
- **Operating Temperature** -40 ~ 85°C (-40 ~ 185°F)
- **Storage Temperature** -40 ~ 85°C (-40 ~ 185°F)
- **Supports Noise Rejection**

Ordering Information

- **ADAM-4510I-AE** Robust RS-422/485 Repeater
- **ADAM-4520I-AE** Robust RS-232 to RS-422/485 Converter
- **ADAM-4117-C** Robust 8-ch Analog Input Module with Modbus

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[ADAM-4117-B](#) [ADAM-4117-C](#)