

# ADAM-5060

# ADAM-5069

## 6-ch Relay Output Module

## 8-ch Power Relay Output Module with LED



ADAM-5060



### Specifications

#### General

- **Certification** CE
- **Connectors** 1 x Plug-in screw terminal (# 14 ~ 22 AWG)
- **Enclosure** ABS+PC
- **Power Consumption** 1.8 W (max.)

#### Relay Output

- **Breakdown Voltage** 500 V<sub>AC</sub> (50/60 Hz)
- **Channels** 2 x form A, 4 x form C
- **Contact Rating**  
AC: 125 V @ 0.6 A  
250 V @ 0.3 A  
DC: 30 V @ 2 A  
110 V @ 0.6 A
- **Insulation Resistance** 1 GΩ min. @ 500 V<sub>DC</sub>
- **Relay Off Time (typical)** 2 ms
- **Relay On Time (typical)** 3 ms
- **Total Switching Time** 10 ms

### Ordering Information

- **ADAM-5060** 6-ch Relay Output Module



ADAM-5069



### Specifications

#### General

- **Certification** CE, FCC class A
- **Connectors** 1 x Plug-in screw terminal (# 14 ~ 22 AWG)
- **Enclosure** ABS+PC
- **LED Indicator**  
On: Active  
Off: Inactive
- **Power Consumption** 2.2 W (max.)

#### Relay Output

- **Breakdown Voltage** 750 V<sub>AC</sub> (50/60 Hz)
- **Channels** 8 x form A
- **Contact Rating**  
AC: 250 V @ 5 A  
DC: 30 V @ 5 A
- **Insulation Resistance** 1 GΩ @ 500 V<sub>DC</sub>
- **Relay On Time (typical)** 5 ms
- **Relay Off Time (typical)** 5.6 ms

### Ordering Information

- **ADAM-5069** 8-ch Power Relay Output Module w/ LED

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[ADAM-5060-AE](#)