

AIMB-562 KIOSK

Intel® Core™2 Duo LGA 775
MicroATX with Dual CRT/LVDS,
10 COM ports, Single LAN



Features

- Intel® 945G/945GC chipset supports 533/800/1066 MHz FSB
- Dual channel DDR2 533/667 MHz SDRAM up to 4 GB
- Supports dual CRT and 24-bit LVDS panel, dual channel 3 W amplifier
- Supports 10 serial ports, 8 USB, 16-bit GPIO
- Supports SUSIAccess and Embedded Software APIs

Software APIs:




Utilities:



Specifications

Processor System	CPU (65 nm/90 nm)	Intel Core 2 Duo	Intel Pentium Dual-Core	Intel Pentium 4	Intel Celeron
	Max. Speed	E7400 2.8 GHz	E2200 2.2 GHz	651 3.4 GHz	440 2.0 GHz
	L2 Cache	4 MB	1 MB	2 MB	512 KB
	Chipset	Intel 945G/945GC + ICH7			
	BIOS	Award 16 Mbit, SPI			
	Front Side Bus	533/800/1066 MHz			
Expansion Slot	PCIe x16	-			
	PCIe x1	250 MB per direction, 1 slot			
	PCI	32-bit/33 MHz, 2 slots			
Memory	Technology	Dual channel DDR2 533/667 MHz SDRAM			
	Max. Capacity	4 GB			
	Socket	2 x 240-pin DIMM (Non-ECC)			
Graphics	Embedded	Intel GMA 950 sharing 224 MB system memory			
	LVDS	Supports single channel 24-bit/dual channel 48-bit LVDS, via Chronitel 7308B SDVO transmitter			
	2nd VGA	Supports 2nd CRT, via Chronitel 7317 SDVO transmitter			
	Dual Display	CRT + LVDS, CRT + CRT			
Ethernet	Interface	10/100/1000 Mbps			
	Controller	GbE LAN: Realtek 8111C			
	Connector	RJ-45 x 1			
SATA II	Max. Data Transfer Rate	300 MB/s			
	Channel	2			
EIDE	Mode	ATA 100/66/33			
	Channel	1 (max. 2 devices)			
I/O Interface	CRT	2			
	USB	8			
	Audio	2 (Line-out, Mic-in)			
	Serial	10 (8 of RS-232; 2 of RS-232/422/485 supports auto flow control)			
	Parallel	1 (SPP/EPP/ECP)			
	FDD	-			
	PS/2	2 (1 x keyboard and 1 x mouse)			
	GPIO	16-bit GPIO			
Watchdog Timer	Output	System reset			
	Interval	Programmable 1 ~ 255 sec/min			
Power Requirements	Power On	Intel Core 2 Duo E4300 1.8 GHz FSB 800 MHz, 1 GB DDR2 667 SDRAM			
		3.3 V	5 V	12 V	5 Vsb
		1.02 A	4 A	2.35 A	0.26 A
Environment		Operating		Non-Operating	
	Temperature	0 ~ 60° C (32 ~ 140° F), depends on CPU speed and cooler solution		-20 ~ 70° C (-4 ~ 158° F)	
Physical Characteristics	Dimensions (W x D)	244 x 244 mm (9.6" x 9.6")			

Block Diagram



Ordering Information

Part Number	Chipset	Display	COM	GbE LAN
AIMB-562VG-KSA1E	945G	2 CRT/LVDS	10	1
AIMB-562VG-GRA1E	945G	2 CRT	10	1
AIMB-562L-KSA1E	945GC	1 CRT	10	1

*We strongly suggest using only Advantech's certified LGA775 CPU coolers to ensure board reliability under harsh conditions.

Riser Card

Part Number	Description
AIMB-R430P-03A2E	2U riser card for 3 PCI expansion

I/O View



AIMB-562VG-KSA1E
AIMB-562VG-GRA1E



AIMB-562L-KSA1E

Packing List

Description	Quantity
IDE HDD cable	1
Serial ATA HDD data cable	2
Serial ATA HDD power cable	2
COM port cable kit	4
I/O port bracket	1
Startup manual	1
Utility CD	1

Optional Accessories

Part Number	Description
1750000334	LGA775 CPU cooler (115 W)
1960022033T000	LGA775 CPU cooler for 2U chassis (2 VGA)
1960046434T000	LGA775 CPU cooler for 2U chassis (1 VGA)
1700008461	USB cable with four ports, 30.5 cm
1700002204	USB cable with dual ports, 27 cm
1700003195	USB cable with dual ports, 17.5 cm
1700008809	Printer port cable
1700000447	1-to-4 serial ports cable kit, 45 cm
1701400181	1-to-4 serial ports cable kit, 18 cm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[AIMB-562L-KSA1E](#)