

Antenna

ANT-LTEMG3-150 Datasheet



1 Product Description

This Advantech external 4G antenna covers main 4G LTE bands and is compatible with 3G/2G/LPWA bands as well. The external antenna is barely influenced by the internal environment of devices, giving a much better performance in efficiency, radiation and gain whilst providing an optimized solution for a customer product. Advantech also offers flexible installation with custom cable length and connector options.

2 Product Features

- Cellular LTE
- High efficiency
- Excellent performance

3 Product Specifications

Passive Electrical Specifications

Frequency Range	700–2700 MHz
Input Impedence	50 Ω
VSWR	≤ 3.0
Gain	≤ 3.5 dBi
Polarization Type	Linear

Detailed Passive Electrical Specifications

Frequency Range (MHz)	698–960	1176–1280	1400–1610	1710–2170	2170–2690	3300–4000	4000–5000	5000–6000
VSWR (Max.)	1.97	-	-	2.3	2.3	-	-	-
Average Efficiency (%)	28	-	-	33	32	-	-	-
Max. Peak Gain (dBi)	3.5	-	-	2.8	3.0	-	-	-

Mechanical Specifications

Antenna Size	318 mm $\times$ Φ 30 mm RG174 Cable Length = 1500 mm
Casing	ABS
Connector Type	SMA Male (Center Pin)
Working Temperature	-40 °C to +85 °C
Radome Color	Black
Mounting Type	Magnet
IP Rating	IP65


4 Overall Performance

4.1. Test Environment

- KEYSIGHT VNA Network Analyzer E5063A 100 kHz – 8.5 GHz
- RayZone®2800 Chamber 5G (FR1) SISO/MIMO, 400 MHz – 8.0 GHz




4.2. VSWR




Frequency (MHz)	700	820	960	1710	2170	2400	2690
VSWR	1.97	1.52	1.86	1.75	1.19	2.28	1.74

4.3. Efficiency




Frequency (MHz)	700	820	960	1710	2170	2400	2690
Efficiency (%)	28.7	28.6	30.4	39.3	24.9	39.5	40.8

4.4. Gain







Frequency (MHz)	700	820	960	1710	2170	2400	2690
Gain (dBi)	3.24	1.53	0.22	2.72	-0.46	1.79	2.69





4.5. Radiation Pattern







4.5.1. 700 MHz







4.5.2. 820 MHz







4.5.3. 960MHz







4.5.4. 1710 MHz







4.5.5. 2170 MHz



4.5.6. 2400 MHz



4.5.7. 2690 MHz



5 Product Size



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[ANT-LTEMG3-150](#)