



GSM ANTENNAS

Antenna GSM Magnetic 30, 3 dB, FME(f), RG174/3m

AO-AGSM-MG3F

SECTRON company offers wide portfolio GSM antennas with various versions differing in shape, level of gain or attachment manner. SECTRON guarantees compatible connection between antenna and all antenna adaptors produced by SECTRON.

BENEFITS

- Low VSWR
- Optimized high frequency Gain
- Flexible




FEATURES

AO-AGSM-MG3F

Technology	GSM
Frequency bands	900, 1800 MHz
Bandwidth	-
Gain	3 dBi
VSWR	<1.8: 1
Impedance	50 ohm
Directivity	-
Beam angle	-
Polarization	Vertical
Maximum input power	10 W
Power voltage	-
Dimensions	30 x 232 mm
Weight	52.9 g
Operating temperature	-30 to +90 ° C
Execution	External
Method of attachment	Magnetic
Cable type	RG174 / U
The cable length	3 m
Connector type	FME (f), SMA(m)

DRAWING



Units: mm

VARIANT	PART NUMBER
Antenna GSM Magnetic 30, 3 dB, FME(f), RG174 3m	AO-AGSM-MG3F
Antenna GSM Magnetic 30, 3 dB, SMA(m), RG174/3m	AO-AGSM-MG3S

CONTACTS

SECTRON s.r.o. Josefa Šavla 1271/12
709 00 Ostrava 9, Czech Republic

WWW.SECTRON.CZ
tel.: +420 556 621 021

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[AO-AGSM-MG3F](#)

[B+B SmartWorx:](#)

[AO-AGSM-MG3S](#)