

APAX-5046

APAX-5046SO

24-ch Digital Output Module

20-ch Source Type DO Module



APAX-5046



Specifications

General

- **Certification** CE, FCC class A
- **Dimensions (W x H x D)** 30 x 139 x 100 mm
- **Enclosure** ABS+PC
- **Weight** 165 g
- **Power Consumption** 2.5 W @ 24 V_{DC} (typical)
- **Status Display** LED per channel
On: Logic level 1
Off: Logic level 0

Digital Output

- **Channels** 24 (Sink Type)
- **Voltage Range** 8 ~ 35 V_{DC}
- **Rated Current Output** 0.5 A (per channel, at signal "1")
- **Leakage Current** 0.1 mA (at signal "0")
- **Switch Rate:** Resistive load: 300 Hz (max.)
Inductive load: 20 Hz (max.)
Lamp load: 200 Hz
(max. at 5W lamp and under 50 Ω, 24 V)

Protection

- 2,500 V_{DC} isolation between channels and backplane
- Short Circuit Protection
- Thermal Shutdown Protection

Environment

- **Operating Temperature** -10 ~ 60°C
(when mounted vertically)
- **Storage Temperature** -40 ~ 70°C
- **Relative Humidity** 5 ~ 95% (non-condensing)

Ordering Information

- **APAX-5046** 24-ch Digital Output Module



APAX-5046SO



Specifications

General

- **Certification** CE, FCC class A
- **Dimensions (W x H x D)** 30 x 139 x 100 mm
- **Enclosure** ABS+PC
- **Weight** 165 g
- **Power Consumption** 2.5 W @ 24 V_{DC} (typical)
- **Status Display** LED per channel
On: Logic level 1
Off: Logic level 0

Relay Output

- **Channels** 20 (Source Type)
- **Voltage Range** 10 ~ 35 V_{DC}
- **Rated Current Output** 1 A (per channel, at signal "1")
- **Leakage Current** 0.1 mA (at signal "0")
- **Switch Rate** Resistive load : 300 Hz (max.)
Inductive load: 20 Hz (max.)
Lamp load: 200 Hz
(max., at 5W amp and under 50 Ω, 24V)

Protection

- 2,500 V_{DC} isolation between channels and backplane
- Short Circuit Protection
- Thermal Shutdown Protection

Environment

- **Operating Temperature** -10 ~ 60° C
(when mounted vertically)
- **Storage Temperature** -40 ~ 70° C
- **Relative Humidity** 5 ~ 95% (non-condensing)

Ordering Information

- **APAX-5046SO** 20-ch Source-Type DO Module

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[APAX-5046-AE](#)