


ASMB-925

Dual LGA3647-P0 Intel® Xeon® Scalable EATX Server Board with 12 DDR4, 5 PCIe x16 + 1 PCIe x8 + 1 PCI, 8 SATA3, 6 USB3.0, Dual 10GbE, IPMI

NEW




Features

- EATX server board with dual Xeon® Scalable processors
- DDR4 2666 MHz RDIMM up to 786 GB (12 LRDIMMs), support Apache Pass
- Five PCIe x16 (Gen3), one PCIe x8 (Gen3), and one PCI slots
- Intel® X557-AT2 dual 10GbE ports
- Eight SATA3 and six USB3.0 ports
- 0 ~ 40 °C ambient operating temperature range

Specifications

Form Factor	EATX form factor	
Processor System	Socket	Intel LGA3647-P0
	CPU type	Intel Xeon Scalable dual processors (CPU cooler should be purchased separately and TDP up to 205W)
Core Logic	Chipset	Intel C621/C622 chipset
Memory	Total slots	12 (1 DIMM per channel)
	Capacity	Maximum 768GB ECC LRDIMM Maximum 384GB ECC RDIMM
	Memory type	DDR4 ECC-REG 2133/2400/2666 MHz DIMM, support Apache Pass
	Memory size	4 GB, 8 GB, 16 GB, 32 GB, 64 GB (LRDIMM)
Expansion Slots	Total PCI/PCI-X/PCIe slots	7
	Slot location 1	PCI, signal from PCH
	Slot location 2	PCIe x16 slot (x16 link), signal from CPU1
	Slot location 3	PCIe x16 slot (x16 link), signal from CPU1
	Slot location 4	PCIe x16 slot (x16 link), signal from CPU0
	Slot location 5	PCIe x16 slot (x16 link), signal from CPU1
	Slot location 6	PCIe x16 slot (x16 link), signal from CPU0
Graphics	VGA	ASPEED AST2500/2510
Storage	SATA controller	Intel C621/C622: 8 x SATA3 (600 MB/s) support software RAID 0,1,5,10
	SAS controller	-
Networking	GbE/10GbE LAN	2 x Intel I210AT / Intel X557-AT2 (dual 10GbE ports for ASMB-925T2 sku only)
Onboard I/O Connector	PSU connector	24-pin SSI power connector + 3 x 8-pin SSI 12 V power connector
	USB connector	4 x USB2.0 ports (two onboard headers) + 2 x USB3.0 ports (one onboard headers) + 1 x Type-A USB2.0 port
	Fan header	7 x 4pin (5 for system + 2 for CPU)
	SMBus	1
	Chassis intruder	1
	Front LAN LED	1
	Audio Header	1
	PS/2 KB/Mouse	1
	Serial port header	1
Rear I/O Connector	External serial port	1
	External USB port	4 (USB3.0)
	VGA port	1
	RJ-45	4 (LAN2 sharing with IPMI function)
	PS/2 KB/mouse	-
Management Solution	Infiniband	-
	Software	-
Monitoring	Out of band remote management	Yes (ASMB-925/ASMB-925T2 sku only)
	CPU temperature	Yes
Watchdog Timer	System Monitoring	Yes
	Output	System reset
Power Requirement	Interval	Programmable 1 ~ 255 sec/min
	Power On	3.3V 5V 12V 5Vsb -12V 12V_8P_0 12V_8P_1
Environment	(205W CPU@2.5GHz DDR4 2400 4G*12)	1.51A 5.19A 0A 0.05A 0A 20.58A 20.08A
	Temperature	Operating 0 ~ 40 °C, depends on CPU speed and cooler solution Non-operating -40 ~ 85 °C
	Humidity	10% ~ 95% 10% ~ 95% (Non condensing)
Physical Characteristics	Dimension (L x H)	304.8 x 330.2 mm (12" x 13")

Block Diagram



Ordering Information

Part Number	Chipset	Memory	GbE/10GbE LAN	IPMI	Graphics
ASMB-925-00A1	C621	DDR4 RDIMM	2/-	-	AST2510
ASMB-925I-00A1	C621	DDR4 RDIMM	2/-	Yes	AST2500
ASMB-925T2-00A1	C622	DDR4 RDIMM	2/2	Yes	AST2500

Packing List

Part Number	Description	Quantity
2061092500	Driver CD	x 1
2001092500	Startup manual	x 1
1700003194	SATA data cables	x 2
1700022749-11	SATA power cables	x 2
1700019748	CPU power cable	x 2
1960076488T000	I/O shield	x 1
1651003167-01	LGA3647 CPU clip	x 2

Optional Accessories

Part Number	Description
PCA-AUDIO-HDA1E	HD Audio-card
PCA-TPM-00A1E	TPM1.2 Module
PCA-TPM-00B1E	TPM2.0 Module
1960081155N001	LGA-3647 narrow CPU cooler for 1U chassis (85W)
1960081603N001	LGA-3647 narrow CPU cooler for 2U/4U chassis (150W)
1960081603N101	LGA-3647 narrow CPU cooler for 4U chassis (205W)
1700028025-01	Dual port USB cable (45 cm) with bracket
1700028042-01	Four port USB cable (45 cm) with bracket
1700028024-01	Dual port USB 3.0 cable (45 cm) with bracket
1701090401	COM port cable with bracket
1960082347T000	For 1U chassis IO shield

I/O View



ASMB-925T2-00A1


ASMB-925-00A1
ASMB-925I-00A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[ASMB-925-00A1](#) [ASMB-925I-00A1](#) [ASMB-925T2-00A1](#)