


ASMB-817

4th Gen Intel® Xeon® Scalable ATX Server Board with 8x DDR5, 3x PCIe x16, 8x SATA 3, 4x USB 3.2 (Gen1), Dual 10GbE, and IPMI



Features

- LGA4677 ATX server board with 4th Gen. Intel Xeon® Scalable processor
- DDR5 4400/4800 MHz RDIMM up to 2TB (8 DIMMs) supports Intel® Optane™ Persistent Memory
- Features 3x PCIe x16, 2x PCIe x8, 1x PCIe x4, and 1x PCIe x1
- Intel® X710 dual 10GbE ports
- Eight SATA 3 and one M.2 connectors (SATA/PCIe compatible)
- 0 ~ 60 °C/ 32 ~ 140 °F ambient operating temperature range


CE FCC

Specifications

Form Factor		ATX form factor				
Processor System	Socket	Intel LGA4677 (Socket E)				
	CPU type	4th Gen Intel Xeon Scalable processors (CPU cooler should be purchased separately*)				
Core Logic	Chipset	Intel C741 chipset				
Memory	Total slots	8x (1 DIMM per channel)				
	Capacity	Maximum 2TB ECC RDIMM				
	Memory type	DDR5 ECC-REG 4400/4800 MHz RDIMM, supports Intel® Optane™ Persistent Memory				
	Memory size	16GB, 32GB, 64GB, 128GB, 256GB				
Expansion Slots	Total PCI/PCI-X/PCIe slots	7				
	Slot location 1	PCIe x1 slot (x1 link), signal from PCH				
	Slot location 2	PCIe x16 slot (x16 link), signal from CPU, CXL support				
	Slot location 3	PCIe x4 slot (x4 link), signal from CPU				
	Slot location 4	PCIe x16 slot (x16 link), signal from CPU, CXL support				
	Slot location 5	PCIe x8 slot open end (x8 link), signal from PCH				
	Slot location 6	PCIe x16 slot (x16 link), signal from CPU, CXL support				
Graphics	VGA	Aspeed AST2600				
	Storage	SATA controller	Intel® C741: 8 x SATA 3 (6 Gb/s), support software RAID 0,1,5,10			
Networking	SAS controller	-				
	GbE/10GbE LAN	2 x Intel® I210AT / Intel® X710-AT2 (dual 10GbE ports)				
Onboard I/O Connector	PSU connector	24-pin SSI power connector + 2 x 8-pin SSI 12 V power connector + 4-pin SSI 12 V power connector				
	USB connector	4 x USB 2.0 ports (two onboard headers) + 2 x USB 3.2 Gen1 ports (one onboard header) + 1 x Type-A USB 2.0 port				
	Fan header	6 x 4-pin (5 for system + 1 for CPU)				
	M.2	1 x M.2 2280/22110 B+M key (SATA and PCIe)				
	SMBus	1				
	Chassis Intrusion	1				
	Front LAN LED	1				
	Audio Header	1				
Rear I/O Connector	PS/2 KB/Mouse	1				
	Serial port header	1				
	External serial port	1				
	External USB port	2x (USB 3.2 Gen1) + 4x USB (2.0)				
	VGA port	1				
	RJ-45	5x (1 port dedicated for IPMI function)				
Management Solution	PS/2 KB/mouse	-				
	Software	-				
Monitoring	Out of band remote management	Yes				
	CPU temperature	Yes				
Watchdog Timer	System Monitoring	Yes				
	Output	System reset				
Power Requirement	Interval	Programmable 1 ~ 255 sec/min				
	Power On	3.3V	5V	5Vsb	12V	12V_8P
	(225W CPU @1.5GHz 4800 64G*8)	1.239A	1.314A	0.7A	0.052A	20.833A
	Environment	Operating	Non-operating			
		Temperature	0 ~ 60 °C/32 ~ 140 °F, depends on CPU speed and cooling solution			
Physical Characteristics	Humidity	-40 ~ 85 °C/-40 ~ 185 °F				
	Dimension (L x H)	10% ~ 95% (Non condensing)				
		304 x 244 mm (12" x 9.6")				

*CPU power design support up to 225W TDP. Please consider extended air thermal solution while using CPU > 205W TDP.

Block Diagram



Ordering Information

Part Number	Chipset	Memory	GbE/10GbE LAN	IPMI	Graphics
ASMB-817T2-00A1	C741	DDR5 RDIMM	2/2	Yes	AST2600
ASMB-817I-00A1	C741	DDR5 RDIMM	2/-	Yes	AST2600

Packing List

Part Number	Description	Quantity
2042081700	Startup manual	x 1
1700003194	SATA data cables	x 2
1700022749-11	SATA power cables	x 2
1700019748	CPU power cable	x 2
1930008089	Screw for M.2 device	x 1
1960076488T001	I/O shield	x 1
1651003739-01	LGA4677 CPU carrier - E1B	x 1

Optional Accessories

Part Number	Description
PCA-AUDIO-HDB1E	HD Audio-card*
PCA-TPMSPI-00A1	TPM 2.0 Module by SPI
1970005575T001	LGA-4677 narrow CPU heatsink for 1U chassis (185W)
1970005860N000	LGA-4677 narrow CPU cooler for 2U/4U chassis (205W)
1700002204	Dual port USB cable (27 cm/10.6 in) with bracket
1700008461	Four port USB cable (30.5 cm/12 in) with bracket
1700020277-01	Dual port USB 3.2 (Gen1) cable (30 cm/11.8 in) with bracket
1701090401	COM port cable (40 cm/15.7 in) with bracket
1700019268-11	PS/2 port cable (35 cm/13.77 in)
1960063434N000	Cable bracket for 1700019268-11
1960082347T001	For 1U chassis I/O shield
1700031684-01	Front panel convert cable

* PCA-AUDIO-HDB1E isn't compatible with 3U chassis

I/O View



ASMB-817T2-00A1



ASMB-817I-00A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[ASMB-817T2-00A1](#) [ASMB-817I-00A1](#)