

96MPI3-2.4-4M10T



Intel® Core™ i3-4330TE Processor (4M Cache, 2.40 GHz)



Features:

- Intel I3-4330TE Processor
- 2 Cores
- 4MB smart cache
- FCLGA1150 Socket Type
- 22NM
- 35W
- Support DDR3-1333/1600



Specifications

Advantech PN	96MPI3-2.4-4M10T
Intel Ordering Code	CM8064601484402
Intel Launch Date	Q3 / 2013
Code Name	Haswell
SPEC Code	SR180
Processor Number	i3-4330TE
# of Cores	2
# of Threads	4
Cache	4MB
Clock Speed	2.4GHz
FSB (Front Side Bus)	5GT/S
Tech. in Nanometer	22nm
Max Design Power	35W

Direct Media Interface	N/A
Socket Type	FCLGA1150
Max Memory Size	32GB
Tcase	72°C
Memory Type	DDR3-1333/1600
Intel® Graphic Processor	N/A
Graphic Base Frequency	350MHz
64-bits Support	YES
Package	Tray
Embedded Channel	YES
RoHS	YES
Compatible Chipset	H87, Q87, Q85, Z87, H81, B85

Compatible Motherboard

Model Number	Description
AIMB-274 Series	Intel® Core™ i7/i5/i3 LGA 1150 Mini-ITX with VGA/DP/HDMI(DP)/LVDS(eDP), 2COM, Dual LAN, PCIe x16
AIMB-784 Series	Intel® 4th Generation Core Processor-based platform

[Learn more on PAPS Website](#)

ADVANTECH

Peripheral Allied Procurement Services

—Your Ultimate Sourcing Partner—

All product specification and compatible chipset are subject to change without notice.

Last updated: 9-Sep-2013

Rev. 1.0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[96MPI3-2.4-4M10T](#)