

96MPXE-2.2-30M20T1



Intel® Xeon® Processor E5-2658A v3 (30M Cache, 2.20 GHz)



Features:

- Intel Xeon E5-2658A v3 Processor
- 12 Cores
- 30MB Cache
- Clock Speed 2.20GHz
- QPI Speed 9.6GT/s
- FCLGA2011-3 Socket Type
- Tech in 22NM
- Max TDP 105W
- Support DDR4-1600/1866/2133



Specifications

Advantech PN	96MPXE-2.2-30M20T1
Intel Ordering Code	CM8064402331600
Intel Launch Date	Q1 / 2015
Code Name	Haswell
SPEC Code	SR27T
Processor Number	E5-2658A v3
# of Cores	12
# of Threads	24
Cache	30MB
Clock Speed	2.20GHz
QPI Speed	9.6GT/s
Tech. in Nanometer	22nm
Max TDP	105W

Direct Media Interface	N/A
Socket Type	FCLGA2011-3
Max Memory Size	768GB
Tcase	91C
Memory Type	DDR4-1600/1866/2133
Intel® Graphic Processor	NO
Graphic Base Frequency	N/A
64-bits Support	YES
Package	Tray
Embedded Channel	YES
RoHs	YES
Compatible Chipset	8900CC, 8903CC, 8910CC, 8920CC, 8925, 8926, 8950, 8955

Compatible Motherboard

Model Number	Description
Learn more on PAPS Website	

ADVANTECH Peripheral Allied Procurement Services - Global Sourcing Local Supports -

All product specification and compatible chipset are subject to change without notice.

Last updated: 16-Nov-2015

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[96MPXE-2.2-30M20T1](#)