



96MPI3-3.5-4M10T

Intel® Core™ i3-4330 Processor (4M Cache, 3.5 GHz)



Features:

- Intel I3-4330 Processor
- 2 Cores
- 4MB smart cache
- Clock Speed 3.5 GHz
- FCLGA1150 Socket Type
- 54W



Specifications

Advantech PN	96MPI3-3.5-4M10T
Intel Ordering Code	CM8064601482423
Intel Launch Date	Q3 / 2013
Code Name	Haswell
SPEC Code	SR1NM
Processor Number	i3-4330
# of Cores	2
# of Threads	4
Cache	4MB
Clock Speed	3.5GHz
FSB (Front Side Bus)	N/A
Tech. in Nanometer	N/A
Max Design Power	54W

Direct Media Interface	N/A
Socket Type	FCLGA1150
Max Memory Size	N/A
Tcase	N/A
Memory Type	N/A
Intel® Graphic Processor	Intel HD Graphics 4600
Graphic Base Frequency	N/A
64-bits Support	YES
Package	Tray
Embedded Channel	YES
RoHS	YES
Compatible Chipset	H87, Q87, Q85, Z87, H81, B85

Compatible Motherboard

Model Number	Description
AIMB-274 Series	Intel® Core™ i7/i5/i3 LGA 1150 Mini-ITX with VGA/DP/HDMI(DP)/LVDS(eDP), 2COM, Dual LAN, PCIe x16
AIMB-784 Series	Intel® 4th Generation Core Processor-based platform

[Learn more on PAPS Website](#)

ADVANTECH

Peripheral Allied Procurement Services

-Your Ultimate Sourcing Partner-

All product specification and compatible chipset are subject to change without notice.

Last updated: 9-Sep-2013

Rev. 1.0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[96MPI3-3.5-4M10T](#)