

96MPCLS-2.3-2M11T



Intel® Celeron G3900TE (2M Cache, 2.30 GHz)



Features:

- Intel Celeron G3900TE Processor
- 2 Cores
- 2MB smart cache
- Clock Speed 2.3 GHz
- FCLGA1151 Socket Type
- Max TDP 35W
- Intel® HD Graphics 510



Specifications

Advantech PN	96MPCLS-2.3-2M11T
Intel Ordering Code	CM8066201938802
Intel Launch Date	Q4 / 2015
Code Name	Skylake
SPEC Code	SR2LU
Processor Number	G3900TE
# of Cores	2
# of Threads	2
Cache	2MB
Clock Speed	2.3GHz
FSB (Front Side Bus)	N/A
Tech. in Nanometer	14nm
Max TDP	35W
Direct Media Interface	8GT/s
Socket Type	LGA1151

Max Memory Size	64GB
Tcase	N/A
Memory Type	DDR4-1866/2133, DDR3L-1333/1600 @ 1.35V
Intel® Graphic Processor	Intel® HD Graphics 510
Graphic Base Frequency	350MHz
PCI-E Revision	3
PCI-E Configuration	Up to 1x16, 2x8, 1x8+2x4
Max # of PCI-E Lanes	16
64-bits Support	Yes
Package	Tray
Embedded Channel	Yes
RoHs	Yes
Compatible Chipset	H170, H110, Z170, Q170, Q150, B150

Compatible Motherboard

Model Number	Description
Learn more on PAPS Website	

ADVANTECH

Peripheral Allied Procurement Services

—Your Ultimate Sourcing Partner—

All product specification and compatible chipset are subject to change without notice.

Last updated: 17-Feb-2016

Rev. 1.0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[96MPCLS-2.3-2M11T](#)