

96MPP-2.3-3M10T



Intel® Pentium® Processor G3320TE (3M Cache, 2.30 GHz)



Features:

- Intel Pentium G3320TE Processor
- 2 Cores
- 3MB cache
- FCLGA1150 Socket Type
- 22NM
- 35W
- Support DDR3-1333/1600



Specifications

Advantech PN	96MPP-2.3-3M10T
Intel Ordering Code	CM8064601484501
Intel Launch Date	Q3 / 2013
Code Name	Haswell
SPEC Code	SR181
Processor Number	G3320TE
# of Cores	2
# of Threads	2
Cache	3MB
Clock Speed	2.3GHz
FSB (Front Side Bus)	N/A
Tech. in Nanometer	22nm
Max Design Power	35W

Direct Media Interface	N/A
Socket Type	FCLGA1150
Max Memory Size	32GB
Tcase	72C
Memory Type	DDR3-1333/1600
Intel® Graphic Processor	YES
Graphic Base Frequency	350MHz
64-bits Support	YES
Package	Tray
Embedded Channel	YES
RoHs	YES
Compatible Chipset	N/A

Compatible Motherboard

Model Number	Description
N/A	N/A

[Learn more on PAPS Website](#)

ADVANTECH Peripheral Allied Procurement Services - Global Sourcing Local Supports -

All product specification and compatible chipset are subject to change without notice.

Last updated: 6-Nov.-2013
Rev. 1.0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[96MPP-2.3-3M10T](#)