


DB9M to DB9F Serial Cables

Models BB-9PAMF1, BB-9PAMF3, BB-9PAMF6,
BB-9PAMF10, BB-9PAMF15, BB-9PAMF25

ADVANTECH

www.advantech.com




PRODUCT FEATURES

- + Fully molded backshell with strain relief for extra protection
- + 28 AWG stranded conductors for flexibility
- + Thumbscrews for tool-less termination
- + DB9 male to DB9 female

ORDERING INFORMATION

MODEL NUMBER	LENGTH
BB-9PAMF1	0.3 meters (1 ft)
BB-9PAMF3	0.9 meters (3 ft)
BB-9PAMF6	1.8 meters (6 ft)
BB-9PAMF10	3.1 meters (10 ft)
BB-9PAMF15	4.6 meters (15 ft)
BB-9PAMF25	7.6 meters (25 ft)

MECHANICAL DIAGRAM



P1	1006	P2
1	1	BROWN
2	2	RED
3	3	ORANGE
4	4	YELLOW
5	5	GREEN
6	6	BLUE
7	7	PURPLE
8	8	GREY
9	9	BLACK
SHIELD		SHIELD

*NOTE: All relevant materials are complied with RoHS directive

5	BLACK PVC TUBE $\varnothing 3.0 \times 22\text{mm}$
	ALUMINUM FOIL 33*65mm
	MOLDED PE COLOR TRANSPARENT
	MOLDED PVC BEIGE
4	NON-UL 9C 28AWG, ALUM-MYLAR FOIL SHIELDING WITH DRAIN WIRE, OD 5.0mm, JACKET BEIGE, DRAWING NO. EMAL2809C-051
3	MOLDED THUMBSCREW #4-40, LENGTH 46.5mm, BEIGE
2	DB9 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR
1	DB9 MALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR

All product specifications are subject to change without notice.
BB-9PAMFxx_0520ds

ADVANTECH

Advantech B+B SmartWorx, 707 Dayton Road, PO Box 1040 Ottawa, IL 61350 USA 1 (800)346-3119/Toll Free | orders@advantech-bb.com | support@advantech-bb.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[B+B SmartWorx:](#)

[9PAMF3](#) [9PAMF15](#) [9PAMF10](#) [9PAMF1](#) [BB-9PAMF1](#) [BB-9PAMF10](#) [BB-9PAMF15](#) [BB-9PAMF3](#)