

DSD-5038

38" Industrial Stretched Signage Display

NEW



Features

- 38" High Resolution Stretched Display (1920 x 538) with LED backlight
- High brightness of 800 nits
- Wide viewing angle (176/176)
- 0 ~ 45° C operating temperature
- Dual signal interface with VGA & DVI, support HDMI-to-DVI converter cable
- Audio phone jack output
- Support VESA-DDC 2B plug & play function
- Wall mounting interface 200x100mm
- Fanless design

Introduction

The Advantech DSD-5038 series Stretched Signage Display Monitor is with innovative size/shape and resolution of the display. The Stretch Display is ideal used for Public Information Display, the ultra wide aspect ratio is perfect for grabbing audience's attention, and the high resolution display gives perfect visual performance in wide variety of applications such as Public Transport Display, Call center, Bar, Digital Signage, Casino, and elevators. The monitor is designed with industrial grade components to ensure the highest standards of reliability are met.

Specifications

Display	Model	DSD-5038N-80A1E
	Size	38" Stretched LED panel
	Resolution	1920 x 538
	Viewing Angle	176° (H)/176° (V)
	Brightness	800 (cd/m²)
	Color Support	16.7M colors
	Contrast Ratio	4000:1
	Response Time	9.5 (gray-to-gray) [msec]
	Backlight Life (hrs)	50,000 hrs
Environment	Operating Temperature	0 ~ 45° C
	Storage Temperature	-10 ~ 60° C
	Humidity	80 %RH Max. (Ta ≤ 45° C), non-condensing
System	I/O	VGA x1; DVI-D x 1; 24 VDC Jack x 1
	OSD	Keys; Menu, Up, Down, Auto Adjust, Monitor Power on/off Menu Functions: Brightness, Contrast, Screen Setting, Color Temp, VGA/DVI, Recall, Auto Adjust
	Power	120 W power adapter, with AC 100 ~ 240 V input and DC +24V @ 5 A output
Power Consumption	ON	76W (Typical); Max <80W
	Standby	3W (Typical); Max <5W
Mechanical	Net Weight	6.4 Kg
	Gross Weight	10.4 Kg
	Dimension	980.9 x 303.2 x 44.4 mm
	Packing	1152 x 180 x 407 mm
	VESA Mounting	200 x 100 (mm)


*Recommend:

(1) Recommended resolution: 1920 x 538

(2) Operating System: Microsoft Windows 7/ Windows 8

Dimensions

Unit: mm



Packing List

Description

DVI cable 2.0 meter
HDMI to DVI cable 1.5 meter
Adaptor AC100-240V 120W +24V/5A

Optional Items

Part Number

Description

1700001524 3-Pin Power Cord (USA)
170203183C 3-Pin Power Cord (EU)
1700008921 3-Pin Power Cord with PSE (Japan)
1700019430 VGA cable 15P(M) 1.8 meter
1700091800 Cable 9P/9P 1.8M M/F (RS232)

Ordering Information

Model Name

Description

DSD-5038N-80A1E 38" 1920 x 538 800cd/m² Stretched Signage Display

Recommend Signage Media Player

Part Number

Description

ARK-DS306 AMD G-Series Signage Media Player
ARK-DS520 Advanced (ION2 based) Graphics Signage Media Player

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[DSD-5038N-80A1E](#)