


PCIE-3030

PCIe 3.0, x8 Crypto/ Compression Intel C625 & C626 Server Adapter



Features

- Controller supports PCI Express Base Specification 3.0 (8 GTs)
- PCI Express x8 lanes
- Intel® QuickAssist Technology for Crypto and Compression
 - Compression/Decompression(Deflate)
 - RSA Decrypt
 - IPSec/SSL, up to 40Gbps
 - Wireless: KASUMI, ZUC, SNOW 3G
 - Bulk: AES, 3DES, RC4
 - Hash: MD5, SHA-1/2 SHA-3 HMAC



Technical Specifications


General Technical Specifications	Interface Standard	PCIe Gen 3.0 (8GTs)
	Board Size(bracket is exclusive)	132.3*68.9 mm (L*H)
	PCI Express Card Type	x8 Lane
	PCI Express Voltage	+12V
		There will not be an external Aux power input
	PCI Connector	Gold Finger: x8
	Controllers	Intel® C625, up to 20Gbps IPSec/SSL Intel® C626, up to 40Gbps IPSec/SSL
	Weight	155gr (5.47oz)
	Power Consumption	20w
	Holder	Metal Bracket: Full height (default) Low profile (accessory)
	Operating Temperature (Required airflow: 300LFM)	-5 ~ 55 °C
	Operating Humidity test	45 °C @ 95%
	Cooling	Passive Heatsink
	Storage Temperature	-40 ~ 85 °C
	Storage Humidity test	60 °C @ 95%
	Regulation	CE/FCC
Operating Systems Support	Operating Systems Support	Linux

Ordering Information

Part Number	Description
PCIe-3030NP-00A1E	PCIe3.0x8 Crypto/Compression Intel C625 Server Adapter
PCIe-3030NP-01A1E	PCIe3.0x8 Crypto/Compression Intel C626 Server Adapter

Dimensions

Unit: mm



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[PCIe-3030NP-00A1E](#) [PCIe-3030NP-01A1E](#) [PCIe-3030NP-02A1E](#)