

Power Supplies

80 Plus PS/2 Single Power Supplies



Part Number	PS8-250ATX-ZE	PS8-300ATX-ZBE	PS8-400ATX-ZE	PS8-500ATX-ZE	PS8-700ATX-ZE
Form Factor	PS/2	PS/2	PS/2	PS/2	PS/2
Wattage	250W	300W	400W	500W	700W
80 Plus Grade	Bronze	Bronze	Bronze	Bronze	Bronze
Input Range	90 ~ 264 V _{AC}	90 ~ 264 V _{AC}	90 ~ 264 V _{AC}	90 ~ 264 V _{AC}	90 ~ 264 V _{AC}
Output Range	+3.3V @ 20 A +5 V @ 21 A +12 V1 @ 16 A +12 V2 @ 16 A -12 V @ 0.3 A -5 V @ 0.3A +5 Vsb @ 2.5 A	+3.3V @ 11.12 A +5 V @ 13.2 A +12 V @ 7.64 A +12 VCPU @ 8 A -12 V @ 0.1 A -5V @ 0.05 A +5 Vsb @ 1.39 A	+3.3V @ 21 A +5 V @ 20 A +12 V1 @ 16 A +12 V2 @ 16 A -12 V @ 0.5 A -5V @ 0.3 A +5 Vsb @ 3 A	+3.3V @ 24 A +5 V @ 20 A +12 V1 @ 16 A +12 V2 @ 16 A -12 V @ 0.5 A -5V @ 0.3 A +5 Vsb @ 3 A	+3.3V @ 24 A +5 V @ 30 A +12 V1 @ 16 A +12 V2 @ 16 A +12 V3 @ 16 A +12 V4 @ 16 A -12 V @ 0.5 A -5V @ 0.5 A +5 Vsb @ 4 A
MTBF(hrs)	100,000 @ 25° C	100,000 @ 25° C	100,000 @ 25° C	100,000 @ 25° C	100,000 @ 25° C
Dimensions (W x H x D)	150 x 86 x 140 mm (5.91" x 3.39" x 5.51")	150 x 86 x 140 mm (5.91" x 3.39" x 5.51")	150 x 86 x 140 mm (5.91" x 3.39" x 5.51")	150 x 86 x 140 mm (5.91" x 3.39" x 5.51")	150 x 86 x 140 mm (5.91" x 3.39" x 5.51")
Safety	CE, FCC, UL, CB, TUV, CCC, KC	CE, FCC, UL, CB, TUV, CCC, KC, BSMI	CE, FCC, UL, CB, TUV, CCC, KC	CE, FCC, UL, CB, TUV, CCC, KC	CE, FCC, UL, CB, TUV, CCC, KC
Compatible Chassis	ACP-2000/IPC-602, ACP-4000, ACP-4010, ACP-4020, ACP-4320, ACP-4340, ACP-4360 IPC-6606, IPC-6608, IPC-5122, IPC-7130, IPC-7130L, IPC-7132, IPC-7220, IPC-510, IPC-610-F, IPC-610-H, IPC-610-L, IPC-611, IPC-619	ACP-2000/IPC-602, ACP-4000, ACP-4010, ACP-4020, ACP-4320, ACP-4340, ACP-4360 IPC-6606, IPC-6608, IPC-5122, IPC-7130, IPC-7130L, IPC-7132, IPC-7220, IPC-510, IPC-610-F, IPC-610-H, IPC-610-L, IPC-611, IPC-619, HPC-5000	ACP-2000/IPC-602, ACP-4000, ACP-4010, ACP-4020, ACP-4320, ACP-4340, ACP-4360 IPC-6606, IPC-6608, IPC-5122, IPC-7130, IPC-7130L, IPC-7132, IPC-7220, IPC-510, IPC-610-F, IPC-610-H, IPC-610-L, IPC-611, IPC-619, HPC-7442	ACP-2000/IPC-602, ACP-4000, ACP-4010, ACP-4020, ACP-4320, ACP-4340, ACP-4360 IPC-6606, IPC-6608, IPC-5122, IPC-7130, IPC-7130L, IPC-7132, IPC-7220, IPC-510, IPC-610-F, IPC-610-H, IPC-610-L, IPC-611, IPC-619, HPC-7442	ACP-2000/IPC-602, ACP-4000, ACP-4010, ACP-4020, ACP-4320, ACP-4340, ACP-4360 IPC-510, IPC-610-F, IPC-610-H, IPC-610-L, IPC-611, HPC-7442

PS/2 DC Power Supplies



Model Name	PS-300ATX-DC48E
Wattage	300W
Input Range	72 ~ 36 V _{DC} , 15 A
Outputs	+5 V @ 30 A (0.3 A min) +3.3 V @ 28 A (0.3 A min) +12 V @ 15 A (0.2 A min) -12 V @ 0.8 A, -5 V @ 0.3 A, +5 Vsb @ 2 A
MTBF (hrs)	100,000 @ 25° C
Dimensions (W x H x D)	150 x 86 x 140 mm (5.91" x 3.39" x 5.51")
Safety	UL, TUV, CB, CCC
Compatible Chassis	ACP-2000, ACP-4000, ACP-4010, ACP-4020, ACP-4320, ACP-4340, ACP-4360, IPC-602, IPC-610

80 Plus 1U/2U Single Power Supplies



Part Number	PS8-500U2-XE	96PS-A700W1U
Form Factor	2U	1U
Wattage	500W	700W
80 Plus Grade	Bronze	Bronze
Input Range	90 ~ 264 V _{AC}	90 ~ 264 V _{AC}
Output Range	+3.3V @ 20 A, +5 V @ 20 A +12 V1 @ 16 A, +12 V1 @ 16 A +12 V3 @ 16 A, -12 V @ 0.5A +5 Vsb @ 3 A	+3.3V @ 24 A, +5 V @ 30 A +12 V1 @ 16 A, +12 V2 @ 16 A +12 V3 @ 16 A, +12 V4 @ 16 A -12V @ 0.5 A, +5 Vsb @ 4 A
MTBF(hrs)	100,000 @ 25° C	100,000 @ 25° C
Dimensions (W x H x D)	70 x 100 x 240 mm (2.75" x 3.93" x 9.44")	40 x 100 x 250 mm (1.57" x 3.93" x 9.84")
Safety	CE, FCC, UL, CB, TUV, CCC, KC	CE, FCC, UL, CB, TUV, CCC, KC
Compatible Chassis	HPC-7242, HPC-7282, HPC-7320, HPC-8316	HPC-7320, HPC-7400, HPC-8316

80 Plus Flex ATX Power Supplies



Part Number	PS8-250FATX-XE	PS8-350FATX-XE
Form Factor	Flex ATX	Flex ATX
Wattage	250W	350W
80 Plus Grade	Bronze	Bronze
Input Range	90 ~ 264 V _{AC}	90 ~ 264 V _{AC}
Output Range	+3.3V @ 12 A +5 V @ 14 A +12 V @ 18 A -12 V @ 0.3 A +5 Vsb @ 2.5 A	+3.3V @ 16A +5 V @ 16 A +12 V1 @ 18 A +12 V2 @ 18 A -12 V @ 0.3A +5 Vsb @ 3 A
MTBF(hrs)	100,000 @ 25° C	100,000 @ 25° C
Dimensions (W x H x D)	81.5 x 40.5 x 150 mm (3.2" x 1.59" x 5.9")	81.5 x 40.5 x 150 mm (3.2" x 1.59" x 5.9")
Safety	CE, FCC, UL, CB, TUV, CCC, KC	CE, FCC, UL, CB, TUV, CCC, KC, BSMI
Compatible Chassis	ACP-1010/ACP-1320, ACP-2010/ACP-2320, ACP-4D00, IPC-3012, IPC-6806S, IPC-6806S-D, IPC-6806, IPC-5120, IPC-7120	ACP-1010/ACP-1320, ACP-2010/ACP-2320, ACP-4D00, IPC-603, IPC-3012, IPC-6806S, IPC-6806S-D, IPC-6806, IPC-5120, IPC-7120, ACP-2020

80 Plus Redundant Power Supplies



Part Number	RPS8-350ATX-XE	RPS8-500ATX-XE	RPS8-750ATX-XE	RPS8-500U2-XE	RPS8-700U2-XE
Form Factor	Mini Redundant	Mini Redundant	Mini Redundant	2U Redundant	CRPS
Wattage	350W 1+1	500W 1+1	750W 1+1	500W 1+1	700W 1+1
80 Plus Grade	Gold	Gold	Gold	Bronze	Gold
PMBus	Ver. 1.2	Ver. 1.2	Ver. 1.2	-	Ver. 1.2
Input Range	90 ~ 264 V _{AC}	90 ~ 264 V _{AC}	90 ~ 264 V _{AC}	90 ~ 264 V _{AC}	90 ~ 264 V _{AC}
Output Range	+3.3V @ 20 A +5 V @ 20 A +12 V1 @ 29 A -5 V @ 0.3 A -12 V @ 0.5 A +5 Vsb @ 2 A	+3.3V @ 20 A +5 V @ 20 A +12 V1 @ 16 A +12 V2 @ 16A +12 V3 @ 16A -5 V @ 0.3 A -12 V @ 0.5 A +5 Vsb @ 3 A	+3.3V @ 24 A +5 V @ 30 A +12 V @ 60.9 A -12 V @ 0.5 A +5 Vsb @ 4 A	+3.3V @ 20 A +5 V @ 25 A +12 V @ 40.2 A -12 V @ 0.5 A +5 Vsb @ 3.52 A	+3.3V @ 25 A +5 V @ 25 A +12 V @ 57 A -12 V @ 0.3 A +5 Vsb @ 4.5 A
MTBF(hrs)	100,000 @ 25° C	100,000 @ 25° C	100,000 @ 25° C	100,000 @ 25° C	100,000 @ 25° C
Dimensions (W x H x D)	150 x 84 x 190 mm (5.9" x 3.3" x 7.48")	150 x 84 x 190 mm (5.9" x 3.3" x 7.48")	150 x 84 x 200 mm (5.9" x 3.3" x 7.87")	85 x 86.6 x 217 mm (3.34" x 3.4" x 8.54")	75.6 x 83.8 x 250 mm (2.97" x 3.29" x 9.84")
Safety	CE , FCC, UL , CB, TUV, CCC, KC	CE , FCC, UL , CB, TUV, CCC, KC	CE , FCC, UL , CB, TUV, CCC, KC	CE , FCC, UL , CB, TUV, CCC, KC	CE , FCC, UL , CB, TUV, CCC, KC
Compatible Chassis	IPC-7130, IPC-7130L, IPC-7220, IPC-610, IPC-611, ACP-4000, ACP-4010, ACP-4320, ACP-4340, ACP-4360, IPC-622, HPC-7442	IPC-7130, IPC-7130L, IPC-7220, IPC-610, IPC-611, ACP-4000, ACP-4010, ACP-4320, ACP-4340, ACP-4360, IPC-622, HPC-7442, IPC-631	ACP-4000, ACP-4010, IPC-622, HPC-7442	HPC-7242, HPC-7282, HPC-7320, HPC-8316, ACP-2020	HPC-7242, HPC-7282, HPC-7320, HPC-8316
Single Module Part Number	96PSRM-A350WMIN	96PSRM-A500W1U-2	96PSRM-A750W1U	96PSRM-A500WFX	-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[96PSRM-A500WFX](#)