

UPOS-P03

Magnetic Stripe Card Reader



Specifications

Product Name	Magnetic Stripe Card Reader
Read Speed	3 – 75 inch/sec
Power Supply	5VDC+/-5%
IO Interface	PS2
Track (ISO TRACK 1,2,3)	track2 bit density is 75 BPI track1/3 bit density is 210 BPI Coercivity of magnetic stripe is 300 Oe to 4000 Oe
Life Cycle	1000000 times
ISO	ISO7811,JIS II
Dimension	29.1x17.5x75(mm)
Environment	Operation Temp. 0 °C — +40 °C Storage Temp. -40 °C — +55 °C

Ordering Information

P/N	Description
UPOS-P03-B117	MSR,PS2 for UPOS-211,black,Slim version

UPOS-P03

MSR + iButton



Specifications

Product Name	MSR + iButton 2 in 1 module
Read Speed	3 – 75 inch/sec
Power Supply	5VDC+/-5%
iButton Key	Dallas Semiconductors iButton keys DS1990A
Track (ISO TRACK 1,2,3)	track2 bit density is 75 BPI track1/3 bit density is 210 BPI Coercivity of magnetic stripe is 300 Oe to 4000 Oe
Life Cycle	1000000 times
ISO	ISO7811,JIS II
IO Interface-MSR	PS2
IO Interface-iButton	PS2
Dimension	29.1x22x75(mm)
Environment	Operation Temp. 0 °C — +40 °C Storage Temp. -40 °C — +55 °C

Ordering Information

P/N	Description
UPOS-P03-B118	MSR+ibutton for UPOS-211,black,Slim version

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[UPOS-P03-A102](#) [UPOS-P03-B113](#) [UPOS-P03-B114](#) [UPOS-P03-A100](#) [UPOS-P03-A101](#) [UPOS-P03-B112](#) [UPOS-P03-B110](#) [UPOS-P03-A104](#) [UPOS-P03-B117](#) [UPOS-P03-B118](#)